




CQB50W8 SERIES 50 WATT 8:1 INPUT ISOLATED DC-DC CONVERTER

Features

- Efficiency Up to 91%
- Fixed Switching Frequency
- Regulated Outputs
- Remote On/Off
- Low No Load Power Consumption
- Fully protected (OTP/OCP/OVP/UVLO)
- 3000Vac I/O Isolation
- Operating Case Temperature -40 to +105°C
- Quarter Brick Size Meet Industrial Standard 2.28"x1.45"x0.5"
- CB Test Certificate IEC62368-1
- UL62368-1 2nd (Reinforce Insulation) Approval
- EN50155 Compliant with External Circuits
- Shock & Vibration EN50155 (EN61373) Compliant
- Fire & Smoke EN45545-2 Compliant
- 5000m Operating Altitude



MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT		INPUT CURRENT		% EFF.		CAPACITOR LOAD MAX.
			MIN.	MAX.	NO LOAD	FULL LOAD	(1)	(2)	
CQB50W8-36S12	9-75 VDC	12 VDC	0 mA	4.17 A	8 mA	1544 mA	91	90	8000uF
CQB50W8-36S15	9-75 VDC	15 VDC	0 mA	3.33 A	8 mA	1542 mA	90	90	6800uF
CQB50W8-36S24	9-75 VDC	24 VDC	0 mA	2.08 A	10 mA	1541 mA	90	90	2350µF
CQB50W8-36S28	9-75 VDC	28 VDC	0 mA	1.79 A	10 mA	1547 mA	90	90	2350µF
CQB50W8-36S48	9-75 VDC	48 VDC	0 mA	1.05 A	10 mA	1556 mA	91	90	700µF

NOTE:

1. Nominal Input Voltage 36 VDC
2. Measured at 48Vin
3. An External Input Capacitor 220uF for All Models are Recommended to Reduce Input Ripple Voltage

PART NUMBER

Series	Nominal Input Voltage	Number of Outputs	Nominal Output Voltage	Remote On/Off Logic	Mounting Inserts
CQB50W8-	II	O	XX	L	-Y (Option)
CQB50W8	36: 36 VDC	S: Single	12: 12VDC 15: 15VDC 24: 24VDC 28: 28VDC 48: 48VDC	None: Positive N: Negative	None: M3x0.5 Mounting Inserts -C: Clear Mounting Insert (3.2mm DIA.)

Part Number Example:

CQB50W8-36S12N-C: Quarter Brick, 50W, 8:1 9-75Vdc Input, Single 12Vdc Output, Negative Logic, Clear Mounting Insert



CQB50W8 Series

TECHNICAL SPECIFICATIONS

(All specifications are typical at nominal input, full load at 25°C unless otherwise noted.)

ABSOLUTE MAXIMUM RATINGS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Input Voltage	Continuous	All	-0.3		75	V _{dc}
Input Surge Voltage	100ms max.	All			100	V _{dc}
Operating Case Temperature	At the Center Part of Base Plate	All	-40		105	°C
Storage Temperature		All	-55		125	°C

INPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Operating Input Voltage		All	9	36	75	V _{dc}
Input Under Voltage Lockout						
Turn-On Voltage Threshold		All	8.4	8.8	9.0	V _{dc}
Turn-Off Voltage Threshold		All	7.6	8	8.2	V _{dc}
Lockout Hysteresis Voltage		All		0.8		V _{dc}
Maximum Input Current	V _{in} =9V, Full Load.	All		6.7		A
No-Load Input Current	V _{in} =36V, I _o =0A	See Model Number Table				mA
Input Filter	Pi filter.	All				
Inrush Current (I ² t)	As per ETS300 132-2.	All			0.1	A ² s
Input Reflected Ripple Current	P-P thru 12uH inductor, 5Hz to 20MHz.	All		30		mA

OUTPUT CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Voltage Set Point Accuracy	V _{in} =36V, Full Load, T _c =25°C	All	-1.0		+1.0	%
Output Voltage Regulation						
Load Regulation	Full Load to No Load	All			±0.2	%
Line Regulation	V _{in} =High Line to Low Line, Full Load	All			±0.2	%
Temperature Coefficient	T _c =-40°C to 105°C	All			±0.02	%/°C
Output Voltage Ripple and Noise (5Hz to 20MHz bandwidth)						
Peak-to-Peak	Full load, 22uF aluminum solid capacitor and 1uF ceramic capacitors	12Vo	150			mV
		15Vo	150			
		24Vo	240			
		28Vo	240			
		48Vo	480			
RMS.		12Vo	80			mV
		15Vo	80			
		24Vo	120			
		28Vo	120			
		48Vo	220			
Output Current Range	V _{in} = 9 to 75V	See Model Number Table				A
Over Current Protection	Hiccup Mode. Auto Recovery.	All	110	150	210	%
Short Circuit Protection		All	Continuous, Auto Recovery.			
External Load Capacitance	Full load (resistive)	See Model Number Table				uF
Output Voltage Trim Range	Po≤max rated power, I _o ≤ I _{o_max}	All	-20		+15	%
Output Voltage Remote Sense Range	Po≤max rated power, I _o ≤ I _{o_max} % of nominal Vo	All			+15	%
Over Voltage Protection	Limited Voltage, % of Nominal Vo	All	117	125	140	%



CQB50W8 Series

EFFICIENCY

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
100% Load	Vin=36V, 48V	See Model Number Table				%

DYNAMIC CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Output Voltage Current Transient						
Error Band	75% to 100% of I_{o_max} step load change $dI/dt=0.1A/us$ (within 1% V_{out} nominal)	All			±5	%
Recovery Time		All			250	us
Turn-On Delay and Rise Time	Full load (Constant resistive load)					
Turn-On Delay Time, From On/Off Control	$V_{on/off}$ to 10% V_{o_set} , Remote On	All		20		ms
Turn-On Delay Time, From Input	V_{in_min} to 10% V_{o_set} , Power Up	All		20		ms
Output Voltage Rise Time	10% V_{o_set} to 90% V_{o_set}	All		10		ms

ISOLATION CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Isolation Voltage (100% factory Hi-Pot tested @2sec.)	1 minute; Input to Output,	All			3000 4200	V_{ac} V_{dc}
	1 minute; Input to Case (Base Plate),	All			2100 3000	V_{ac} V_{dc}
	1 minute; Output to Case (Base Plate)	All			1500 2100	V_{ac} V_{dc}
Isolation Resistance	Input to Output	All	100			MΩ
Isolation Capacitance	Input to Output	All		1000		pF
	Input to Case (Base Plate)	All		None		
	Output to Case (Base Plate)	All		1000		

FEATURE CHARACTERISTICS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
Switching Frequency	Pulse wide modulation (PWM), Fixed	All	180	200	220	KHz
On/Off Control, Positive Remote On/Off logic, Refer to -Vin pin.						
Logic Low (Module Off)	$V_{on/off}$ at $I_{on/off}=1.0mA$	All	0		1.0	V
Logic High (Module On)	$V_{on/off}$ at $I_{on/off}=0.0uA$, Pin open=On	All	4.0		75	V
On/Off Control, Negative Remote On/Off logic, Refer to -Vin pin						
Logic High (Module Off)	$V_{on/off}$ at $I_{on/off}=0.0uA$, Pin open=Off	All	4.0		75	V
Logic Low (Module On)	$V_{on/off}$ at $I_{on/off}=1.0mA$	All	0		1.0	V
On/Off Current (for both remote on/off logic)	$I_{on/off}$ at $V_{on/off}=0V$	All		0.3	1	mA
Leakage Current (for both remote on/off logic)	Logic High, $V_{on/off}=15V$	All			30	uA
Off Converter Input Current	Shutdown input idle current	All		5	10	mA
Over Temperature Shutdown	Temperature at the Center Part of Base Plate, Non-Latching	All		110		°C
Over Temperature Recovery		All		100		°C

GENERAL SPECIFICATIONS

PARAMETER	NOTES and CONDITIONS	Device	Min.	Typ.	Max.	Units
MTBF	$I_o=100\%$ of I_{o_max} ; MIL-HDBK - 217F_Notice 1, GB, 25°C	36S12		663		K hours
		36S15		759		
		36S24		750		
		36S28		740		
		36S48		780		
Weight		All		66		grams
Case Material	Plastic, DAP, UL 94V-0					



CQB50W8 Series

Base plate Material	Aluminum		
Potting Material	UL 94V-0		
Pin Material	Base: Copper Plating: Nickel with Matte Tin		
Shock/Vibration	MIL-STD-810F/EN61373 Compliant		
Humidity	95% RH max. Non Condensing		
Altitude	5000m Operating Altitude, 12000m Transport Altitude		
Thermal Shock	MIL-STD-810F		
Fire & Smoke	EN45545-2 Compliant		
EMI	Meets EN55032 & EN50155 Compliant (with external filter)		Class A
ESD	EN61000-4-2	Level 3: Air ±8kV, Contact ±6kV	Perf. Criteria A
Radiated immunity	EN61000-4-3	Level 3: 80~1000MHz, 20V/m	Perf. Criteria A
Fast Transient	EN61000-4-4	Level 3: On power input port, ±2kV, external input capacitor required	Perf. Criteria A
Surge	EN61000-4-5	Level 4: Line to earth, ±4kV, Line to line, ±2kV	Perf. Criteria A
Conducted immunity	EN61000-4-6	Level 3: 0.15~80MHz, 10V	Perf. Criteria A
Interruptions of Voltage Supply	EN50155	Class S3: 20ms interruptions	Perf. Criteria A
Supply Change Over	EN50155	Class C2: During a supply break of 30 ms,	Perf. Criteria A
Application Note Link		CQB50W8-36S Series App Notes	
Packaging Information Link		Packaging Information	

Immunity to Environmental Conditions.

Phenomenon	EN50155; 2017 Reference Clause(s)	Reference Standard	Test Conditions	Result
Low Temperature Start-up test	13.4.4	EN 60068-2-1	Class OT6 Temperature: -40°C Duration: 2 hrs	Pass
Dry Heat Test	13.4.5	EN 60068-2-2	Class OT6 & ST2 Temperature: 85°C Duration: 6 hrs Extended temperature: 100°C Extended Duration: 10min	Pass
Low Temperature Storage Test	13.4.6	EN 60068-2-1	Temperature: -40°C Duration: 16 hrs	Pass
Cyclic Damp Heat Test	13.4.7	EN 60068-2-30	Temperature: 25°C - 55°C Humidity: 90% RH Duration: 48 hrs	Pass
Random Vibration Test	13.4.11	EN 61373	Temperature: 25°C $\pm 10^{\circ}\text{C}$ Humidity: 50% $\pm 25\%$ RH Frequency range: 5 ~ 150 Hz Vertical: 1.01 m/s^2 Transverse: 0.450 m/s^2 Longitudinal: 0.700 m/s^2 Duration: 10 min / axis	Pass
Simulated Long Life Test at Increased Random Vibration Levels	13.4.11	EN 61373	Temperature: 25°C $\pm 10^{\circ}\text{C}$ Humidity: 50% $\pm 25\%$ RH Frequency range: 5 ~ 150 Hz Vertical: 5.72 m/s^2 Transverse: 2.55 m/s^2 Longitudinal: 3.96 m/s^2 Duration: 5 hrs / axis	Pass
Shock Test	13.4.11	EN 61373	Temperature: 25°C $\pm 10^{\circ}\text{C}$ Humidity: 50% $\pm 25\%$ RH Frequency range: 5 ~ 150 Hz $\pm$ -Vertical: 30 m/s^2 $\pm$ -Transverse: 30 m/s^2 $\pm$ -Longitudinal: 50 m/s^2 Duration: 30ms x18 (Each axis 3 shocks)	Pass



CQB50W8 Series


EN45545-2 Fire & Smoke Test Conditions.

Item		Standard	Hazard Level
R22	Oxygen Index Test	EN 45545-2: 2013 EN ISO 4589-2: 2006	HL1, HL2, HL3
	Smoke Density Test	EN 45545-2: 2013 EN ISO 5659-2: 2013	HL1, HL2
	Smoke Toxicity Test	EN 45545-2: 2013 NF X70-100: 2006	HL1, HL2, HL3
R23	Oxygen Index Test	EN 45545-2: 2013 EN ISO 4589-2: 2006	HL1, HL2, HL3
	Smoke Density Test	EN 45545-2: 2013 EN ISO 5659-2: 2013	HL1, HL2, HL3
	Smoke Toxicity Test	EN 45545-2: 2013 NF X70-100: 2006	HL1, HL2, HL3
R24	Oxygen Index Test	EN45545-2: 2013 EN ISO 4589-2	HL1, HL2, HL3
R25	Glow - Wire Test	EN 45545-2:2013 EN 60695-2-11:2001	HL1, HL2, HL3
R26	Vertical Flame Test	EN 45545-2: 2013 EN 60695-11-10: 2013	HL1, HL2, HL3


CHARACTERISTIC CURVE

Power Derating Curve


**CQB50W8-36S Derating Curve
without Heatsink (Vin=36V)**



**CQB50W8-36S Derating Curve
with Heatsink QBL127 (Vin=36V)**



**CQB50W8-36S Derating Curve
with Heatsink QBT210 (Vin=36V)**







CQB50W8 Series

Performance Data


CQB50W8-36S12
Eff Vs Io @25 Deg. C




CQB50W8-36S12
Pd Vs Po @25 Deg. C




CQB50W8-36S15
Eff Vs Io @25 Deg. C




CQB50W8-36S15
Pd Vs Po @25 Deg. C




CQB50W8-36S24
Eff Vs Io @25 Deg. C




CQB50W8-36S24
Pd Vs Po @25 Deg. C



CQB50W8-36S28
Eff Vs Io @25 Deg. C




CQB50W8-36S28
Pd Vs Po @25 Deg. C





CQB50W8-36S48
Pd Vs Po @25 Deg. C



All Dimensions In Inches(mm)
Tolerances Inches: X.XX= ± 0.02 , X.XXX= ± 0.010
 Millimeters: X.X= ± 0.5 , X.XX= ± 0.25

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[CQB50W8-36S12](#) [CQB50W8-36S12N](#) [CQB50W8-36S15](#) [CQB50W8-36S15N](#) [CQB50W8-36S24](#) [CQB50W8-36S24N](#) [CQB50W8-36S28](#) [CQB50W8-36S28N](#) [CQB50W8-36S48](#) [CQB50W8-36S48N](#) [CQB50W8-36S12-CMFC](#)
[CQB50W8-36S12-CMFD](#) [CQB50W8-36S12N-CMFC](#) [CQB50W8-36S12N-CMFD](#) [CQB50W8-36S15-CMFC](#)
[CQB50W8-36S48-CMFD](#) [CQB50W8-36S48N-CMFC](#) [CQB50W8-36S48N-CMFD](#) [CQB50W8-36S24N-CMFD](#)
[CQB50W8-36S28-CMFC](#) [CQB50W8-36S28-CMFD](#) [CQB50W8-36S28N-CMFC](#) [CQB50W8-36S28N-CMFD](#)
[CQB50W8-36S48-CMFC](#) [CQB50W8-36S15-CMFD](#) [CQB50W8-36S15N-CMFC](#) [CQB50W8-36S15N-CMFD](#)
[CQB50W8-36S24-CMFC](#) [CQB50W8-36S24-CMFD](#) [CQB50W8-36S24N-CMFC](#)