



CFM150S SERIES

150 WATT I.T.E AC-DC POWER SUPPLY WITH PFC



Features


- * Universal Input 90-264Vac
- * 2"x 4" Open Frame Compact Size
- * 120W with Natural Convection
- * 150W with Base Cooling
- * No Load Input Power Consumption<150mW
- * Active PFC Function
- * High Efficiency up to 94%
- * Continuous Short Circuit Protection
- * Meets IEC/EN60335-1/60601-1
- * EMI Safety Meets Class I & Class II
- * Operating Altitude 5000m

Ordering information

CFM150SXXX - X

Blank

B: Base Cooling



MODEL	OUTPUT VOLTAGE	OUTPUT CURRENT		RIPPLE & NOISE NOTE 1	VOLTAGE ACCURACY NOTE 2	VOLTAGE ADJ. RANGE	LINE REGULATION NOTE 3	LOAD REGULATION NOTE 4	% EFF. (Typ.) NOTE 5
		Natural Convection	Base Cooling						
CFM150S120	12V	10.0A	12.5A	1%	±1%	±8%	±0.5%	±1%	93%
CFM150S240	24V	5.0A	6.25A	1%	±1%	±8%	±0.5%	±1%	94%
CFM150S280	28V	4.28A	5.35A	1%	±1%	±8%	±0.5%	±1%	94%
CFM150S360	36V	3.33A	4.16A	1%	±1%	±8%	±0.5%	±1%	94%
CFM150S480	48V	2.5A	3.125A	1%	±1%	±8%	±0.5%	±1%	94%

CFM150S Series Derating Curve



Voltage	90~264Vac
Frequency	47 to 63Hz
Inrush Current	Cold start @25°C 100A max. @240Vac
Input Current	100Vac/2A max., 240Vac/0.8Amax.
Leakage Current	100uA max.

Holdup Time	25ms typ.20ms min. @115Vac
Short Circuit Protection	Hiccup Mode (Auto Recover)
Over Voltage Protection	Latch
Temperature Coefficient	±0.05%/°C


Isolation	Input to output = 3000VAC
Operating Temperature	-30 ~ 80℃ (see derating curve)
	-40℃ can be Start-Up
Storage Temperature	-40 ~ 85℃
Humidity	93% RH max. Non condensing
Switching Frequency	115 KHz Typical
MTBF..... MIL-HDBK-217F, GB, 25℃/115VAC	350Khrs min.
Altitude	5000m
Life Time	26000 hours min.@ 75% load ,40℃
Dimensions	4.00x2.00x1.283 Inches (101.6x50.8x32.6mm)
	-B 4.598x2.00x1.362 Inches (116.8x50.8x34.6mm)
Weight	CFM150SXXX 200g
	CFM150SXXX-B 240g

Emission and Immunity ... EN55032 Class B, FCC Part 15 Class B **(NOTE 7)**
EN61000-3-2, EN61000-3-3, EN61000-6-3, EN61000-6-4
Immunity EN55024, EN61204-3, EN61000-6-1, EN61000-6-2
Safety Class I & Class II, IEC/EN/UL62368-1

1. Add a 0.1uF ceramic capacitor and a 10uF E.L. capacitor to output for ripple & noise measuring @20MHz BW.
2. Voltage accuracy is set at full load.
3. Line regulation is measured from 100Vac to 240Vac with full load.
4. Load regulation is measured from 10% to 100% full load.
5. Typical efficiency at 230 VAC and full load at 25°C.
6. Standard input and output connectors (CN1 and CN2) wafer with TAIWAN KING PIN TERMINAL PVHI series and mate with JST housing VHR series or equivalent.
7. Class I: Radiation & Conduction Class B
Class II: Radiation Class A ; Conduction Class B



All Dimensions are in inches[mm]
Tolerance:Inches:X.XXX±0.02
Millimeters:X.XX±0.5



2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[CFM150S120](#) [CFM150S280-B](#) [CFM150S360](#) [CFM150S480-B](#) [CFM150S480](#) [CFM150S280](#) [CFM150S360-B](#)
[CFM150S240-B](#) [CFM150S120-B](#) [CFM150S240](#)