

Series 06TR

6 mm Trimmer Potentiometer

- Terminals: tinned brass or tinned steel.
- Flexible gull-wing / through hole / "J" bend terminal configurations
- Various rotor types and with optional shaft & Wheel configurations
- IP 54 according to IEC 60529

Description

6 mm carbon potentiometers with plastic housing. Plastic materials can be self-extinguishable according to UL 94 V-0 upon request. This product is ideal for dimmers, volume/lighting regulation, timers and relays in industrial, electronics and automotive applications.

Ordering Information

Series	Rotor	Model	Taper	Resistance Value	Tol.	Terminal Material	Packg.	Special Request*
06TR	1	A	A	101	A	P	R	Extra Features Assembled Accessories
	Rotor type (Page 4)	Model type (Page 4-6)		Resistance Value		Terminal Material		Extra Features
	1: D-type	A: H2.5		101=100Ω		P: Tinned brass		Life (standard 1,000 cycles)
	2: M-type	B: HSMD		201=200Ω		S: Tinned steel (Only available for Through-hole models)		Track
	3: N-type	C: V2.5		...				Detents
	4: X-type	D: V5		505=5MΩ				Housing
		E: VS5						Rotor
		F: VSMD						Wiper
		G: VESMD						
					Tol.			
					A: ±5%			
					B: ±10%			
					C: ±20%			
					D: ±25%			
					E: ±30%			
					F: +50%/-30%			
						Packaging		
						Blank: Bulk		
						R: Tape & Reel		
								Accessories
								Assembly (Shaft & Wheel)
								Ref#
								Color
								Flam
								Connect
								Operating temperature

*Please contact CTS representatives for the special requests.

Standard Configuration	Through-hole	SMD
Dimensions:	6mm	
Protection:	IP 54 (high level of protection against dust and also against water splashing) On request: Self-extinguishable, to meet UL 94 V-0	
Substrate:	Carbon technology	Carbon technology (Special for high temperature)
Color:	Blue housing + white rotor	Brown housing + grey rotor
Packaging:	Bulk or Tape & Reel	
Wiper position:	at 50% $\pm 15^\circ$	
Terminals: *	Snap in P (except model 06TRVS5)	---
Marking:	Resistive value marked on housing. Others on request.	

* By default, terminals are always crimped (with snap in, "SNP") to better hold the component to the PCB during the soldering operation except VS5, with short terminals that do not allow for SNP. CTS can provide straight terminals if needed. Also, there is an option of having shorter terminal tips.

SNP



Electrical Specifications

	Through-Hole	SMD
Range of resistance values*		
Lin (A)	100 Ω \leq Rn \leq 5M Ω	100 Ω \leq Rn \leq 1M Ω
Log (B) Antilog (C)	1 K Ω \leq Rn \leq 2M2 Ω	1 K Ω \leq Rn \leq 1 M Ω
Tolerance*:		
Rn < 100 Ω :	+50%, -30% (out of range)	-
100 Ω \leq Rn \leq 100K Ω	$\pm 20\%$	$\pm 25\%$
100K < Rn \leq 1M Ω :	$\pm 20\%$	$\pm 25\%$
1M Ω < Rn \leq 5M Ω :	$\pm 30\%$	$\pm 50\%$
Rn > 5M Ω :	+50%, -30% (out of range)	-
Residual Resistance	Rn \leq 400 Ω \leq 2 Ω ; Rn > 400 Ω 5*10 ⁻³ * Rn	
CRV - Contact Resistance Variation (dynamic)	Electrical Angle 215 $^\circ$ $\pm 20^\circ$ \leq 3%Rn. Other tapers, please inquire	
Max Power Dissipation	at 50 $^\circ$ C 0.10W-Lin(A) 0.06W -Log(B), Antilog(C)	
Max. Voltage	100VDC-Lin(A) 60VDC-Log(B), Antilog(C)	
Operating Temperature Range	-25 $^\circ$ C to +70 $^\circ$ C (+85 $^\circ$ C on request)	
Temperature Coefficient		
100 Ω \leq Rn \leq 10K Ω	+200 / -300 ppm	+200 / -500 ppm
10K Ω \leq Rn \leq 5M Ω	+200 / -500 ppm	+200 / -1000 ppm

* Out of range ohm values and tolerances are available on request.


Mechanical and Environmental

Actuation Life	1,000 cycles. On Request: Long Life
Angle of rotation (mechanical)	235° ± 10°
Angle of rotation (electrical)	215° ± 20°
Wiper standard delivery position	50% ± 15%
Max. stop torque	4 Ncm
Max. push/pull on rotor	9.8 N
Wiper Torque	< 2Ncm

Recommended Soldering Conditions (Lead free, RoHS compliant)

Manual soldering	Reflow soldering SMD	Flow (wave) soldering
Soldering tools of 20W max.	Preheating temperature: Max 150°C; 60-90 s	Recommended Alloy: SnAgCu
Maximum temperature of soldering tools: 280°C Time: 3 s. max.	Temperature Ramp-up: 2-3°C / s. Solder temperature: 240°C for 5 ± 1 s.	Preheating stage: Max 100°C; 30-60 s. Temperature Ramp-up: 1.2-2.5°C/s. Max. wave temp.: 260°C for 4s., (245°C recommended) Time within +0°-10°C of peak: 10s.
		Cooling rate: 5°C/s.

Tapers



Mechanical Specifications


Rotor

Rotors are drawn in their standard positioning, 50% of rotation. Alternative delivery positioning can be requested. Accessories in this catalogue are designed for the X rotor, unless otherwise stated.




Surface Mount Gull Wing Terminal

HSMD




VSMD




Surface Mount J-bend Terminal

VESMD




Thru-hole Terminal


H2.5




V2.5



VS5



V5




Shaft

Shafts are available in different colors and with self-extinguishable property, according to UL 94 V-0, under request. CTS can study special shaft designs.


Shafts can be sold separately or delivered already mounted on the potentiometer at CTS.

When a shaft is mounted, the distance from the top of the potentiometer to the top of the shaft is marked with "L" in the table below, as shown in the drawings:

H potentiometer + shaft



V potentiometer + shaft




Shaft	6022	6023	6031	6024	6025	6028	6040
L Dimension	10	10	11	12.2	14.5	14.5	21.3


6022




6023




6024




6025




6028



6031



6040




Wheel


Thumbwheels are available in different colors (color chart in “order information” section) and with self-extinguishable property according to UL 94 V-0, under request. Thumbwheels can be mounted on the potentiometers at CTS (see models with WT-6030 or WT-6037) or sold separately. CTS can study special thumbwheel designs.

6001


6001




6030




6032




6034




6035 (Designed for M rotor)



6037






6043




Packaging

Bulk packaging:	With shaft or thumbwheel inserted	Pieces per box
H2,5	None, only potentiometers.	3,000
V2,5 - V5 - VS5	None, only potentiometers.	2,500
HSMD - VSMD - VESMD	None, only potentiometers.	3,000
H2,5 - V2,5 - V5 - VS5 - HSMD - VSMD - VESMD	6001, 6030, 6032, 6035, 6037, 6043 6024, 6025, 6028 6022, 6023, 6031	2,000 500 1,250
Tape & Reel packaging:	With thumbwheel inserted?	
VSMD	None, only potentiometers.	13" Reel (Standard), with 24mm width tape 1,200 pcs per reel, 12mm step between cavities.
	6030, 6035, 6037	750 pcs per reel, 12mm step between cavities.

VESMD	None, only potentiometers.	1.000 pcs per reel, 12mm step between cavities.
	6030, 6035, 6037	700 pcs per reel, 12mm step between cavities.
HSMD	None, only potentiometers.	750 pcs per reel, 12mm step between cavities.
	With specific thumbwheel.	Under request.
VS5...PIP	None, only potentiometers.	900 pcs per reel, 12mm step between cavities.



13" Reel



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

[06TR4FA503DPR](#) [06TR4BA104DPR](#) [06TR4AA503CP](#) [06TR4FA103DPR](#) [06TR4AA103CP](#) [06TR4DA103CP](#)
[06TR4AA104CP](#) [06TR4DA503CP](#) [06TR4FA104DPR](#) [06TR4BA103DPR](#) [06TR4BA503DPR](#) [06TR4DA104CP](#)