


GOT321B-ADL-WCD NEW

21.5" FHD Fanless Touch Panel Computer with LGA1700 Socket 14th/13th/12th Gen Intel® Core™ i9/i7/i5/i3 or Pentium® Processor



- | | |
|--|-------------------------|
| 1. Power button | 7. Gigabit LAN |
| 2. Phoenix type connector for DC power input | 8. COM1 |
| 3. Grounding hole | 9. HDMI 1.4b |
| 4. Remote power switch | 10. Line-out |
| 5. USB 3.2 Gen1 | 11. COM2 |
| 6. USB 2.0 | 12. Flexible I/O window |



▲ Side view



▲ Rear view



Fanless



IP65



Wide Temp.

Features

- 21.5" FHD TFT LCD with 400 nits of brightness
- 10-point PCAP multi-touch panel
- Supports one 2.5" SATA HDD/SSD
- Supports 2 HDMI outputs for second display
- Supports WLAN module and antenna (optional)
- Supports 4 USB and 2 COM ports
- Flexible I/O window with support for COM3, and DIO (optional)
- Supports panel mount, VESA mount, desktop stand, and wall mount
- Wide temperature range of -10 to +50°C



Introduction

The GOT321B-ADL-WCD is a sleek 21.5" FHD TFT LCD multi-touch panel PC, offering fanless operation and support for LGA1700 socket 14th/13th/12th gen Intel® Core™ i9/i7/i5/i3 or Pentium® processor. It is equipped with M.2 Key E and PCIe Express Mini Card slots for easy integration of Wi-Fi modules, perfect for enhancing connectivity in factory automation and oil pipe monitoring systems.

21.5" FHD TFT LCD with projected capacitive touch

The 21.5" FHD TFT LCD touch panel PC supports a brightness of 400 nits, providing crisp FHD resolution display capability. Its fanless design and flat-panel touch screen enhance user intuitiveness, ensuring a seamless and user-friendly experience.

Specifications

Front Bezel	IP65 front bezel	
LCD Panel	Display Type	21.5" FHD TFT LCD
	Brightness (cd/m ²)	400 nits
	Resolution	1920 x 1080
Main System	CPU	LGA1700 socket 14th/13th/12th gen Intel® Core™ i9/i7/i5/i3 or Pentium® processor (up to 35W)
	Chipset	Intel® H610
	System Memory	1 x 260-pin DDR4 3200MHz SO-DIMM, up to 32GB
	BIOS	AMI UEFI BIOS
	Storage	1 x 2.5" SATA HDD (WT)/SSD (7 mm and 9.5 mm height, removable)
	Watchdog Timer	255 levels, 0 to 255 sec.
	Onboard Graphics	Intel® UHD Graphics 770
I/O Connector	1 x 9-pin D-sub Male RS-232/422/485	
	1 x RS-232	
	1 x Flexible I/O window with support for COM3, and DIO (optional)	
	1 x RJ-45 for 10/100/1000Mbps (Intel® I219-V)	
	1 x RJ-45 for 10/100/1000/2500Mbps (Intel® I225-V)	
	2 x USB 3.2 Gen1 (Type A)	
	2 x USB 2.0 (Type A)	
	1 x Phoenix type connector for DC power input	
	1 x Switch for power on/off (ATX)	
	1 x Line-out	
	2 x HDMI 1.4b	
	1 x Remote power switch	
	1 x Grounding hole	
TPM	TPM 2.0	
Expansion Interface	1 x M.2 Key E 2230 with PCIe x1 and USB 2.0	
	1 x PCI Express Mini Card (USB+PCIe signal+nano SIM slot "LTE")	
Touchscreen	Projected capacitive touch	
Power Supply	10 to 36V DC-in (typical 12/24VDC) via terminal block	
Power Consumption	120W	
Dimensions (W x D x H)	542 x 76.4 x 338 mm (21.34" x 3.01" x 13.31")	
Packing Dimensions (W x D x H)	720 x 205 x 540 mm (28.35" x 8.07" x 21.26")	
Weight (net/gross)	8.7 kg (19.18 lb)/12.40 kg (27.34 lb)	
Operating Temperature	-10°C to +50°C (35W CPU/SSD)	
Relative Humidity	10% to 95% @ +40°C; non-condensing	
Operation Vibration	1G/5 to 500Hz/operation (SSD, random)	
Certifications	CE Class A, IEC/EN 61000-6-4, and IEC/EN 61000-6-2	
	FCC 47 CFR Part 15 Subpart B (Class A)	
	UKCA	
	RoHS standard	

Ordering Information

GOT321B-ADL-WCD (P/N: E22B321B00)	21.5" FHD TFT fanless touch panel computer with LGA1700 socket 14th/13th/12th gen Intel® Core™ i9/i7/i5/i3 or Pentium® processor (up to 35W), 10-point projected capacitive multi-touch screen, and 10 to 36V DC-in terminal block connector
-----------------------------------	--

* Other configuration by request

* Specification and certifications may vary based on different requirements



Packing List

1 x GOT321B-ADL-WCD
1 x Panel mount kit set
1 x Phoenix connector

Optional Accessories

4G LTE Kit	
Wi-Fi kit	
594K6220210E	Remote power cable, L= 720 mm
E29R131114	Wall mount kit
50906A24000E	Adapter 24V230W FSP230-AAAN3 WIRE FSP
509000001500	Adapter 24V120W FSP120-AAAN3 WIRE FSP
E392902103	AX92902 + AX93287 full-size PCI Express Mini module with Gigabit LAN
E392903102	AX92903 full-size PCI Express Mini module with CAN Bus
E392906101	AX92906 full-size PCI Express Mini module with COM
E392918103	AX92918 full-size PCI Express Mini module with 2 Gigabit LAN

Optional OS Installation

Win 10, Win 10 IoT, Win 11, Win 11 IoT, and Linux

Dimensions

