



VR CONNECTOR

3.96 mm/Wire-to-Board connectors/ IDC style (Insulation displacement connector) and Mating style

End connection



Daisy chain connection



The VR series is a 3.96 mm pitch wire-to-board connector for 7 A rated power supply circuits. Furthermore, it can accommodate AWG #18 wire, which is rare for an IDC connector.

■ Features

• Twin U-slot insulation displacement section

The contacts built into the socket connect to the post with base at two separate points, in both the front and back areas, ensuring a high performance, stable electrical connection.

• Two wiring styles

Two wiring styles are possible, including daisy chain through connections and end connections, depending on the circuit design.

■ Specifications

- Current rating: 7 A AC/DC (AWG #18)

Note) Notes on parallel branching current:

Do not branch to the multiple circuits in parallel current which is exceeds the rated current, as it may cause problems such as imbalance when applying current.

If it is unavoidable that branch in parallel is necessary, design the circuits while suppressing the unbalanced current and proving the sufficient margin to the rated current.

- Voltage rating: 250 V AC/DC

- Temperature range: -25°C to +85°C

(including temperature rise in applying electrical current)

- Contact resistance:

Initial value/ 10 mΩ max.

After environmental tests/ 20 mΩ max.

- Insulation resistance: 1,000 MΩ min.

- Withstanding voltage:

There shall be no breakdown or flashover while applying 1,500 VAC for one minute.

- Applicable wire range:

UL style No./ UL1007

Note) Please contact JST for details regarding the use of other UL style wires.

Conductor size/ AWG #26, AWG #24, AWG #22, AWG #20, AWG #18

Conductor composition/

AWG #26, AWG #24, AWG #22:
7 strands, tin-coated

AWG #20: 7 strands, 26 strands,
tin-coated

AWG #18: 34 strands, 43 strands

Insulation O.D./ φ 1.3 mm to φ 2.1 mm

- Applicable PC board thickness: 0.8 mm to 1.6 mm

- * Please refer to the "Handling Precautions for Terminals and Connectors" on our website (listed in the "Technical Documents" column on the Product Information page) before use.

* RoHS2 compliance

* Dimensional unit: mm


* Contact JST for details.

■ Standards

For information on overseas standard registrations, please refer to the "List of Registered Overseas Standards" on our website (listed in the "Technical Documents" column on the Product Information page).

* Specifications registered to overseas standards may differ from the general specifications listed above.

Socket



No. of circuits	Model No.					Dimensions (mm)		Q'ty/bag
	For AWG #26 Line color: No color	For AWG #24 Line color: black	For AWG #22 Line color: red	For AWG #20 Line color: brown	For AWG #18 Line color: orange	A	B	
2	—	—	—	02VR-AN	02VR-BO	3.96	7.92	2,000
3	—	03VR-4K	03VR-2R	03VR-AN	03VR-BO	7.92	11.88	1,000
4	—	—	—	04VR-AN	04VR-BO	11.88	15.84	1,000
5	—	—	—	—	05VR-BO	15.84	19.80	1,000
6	—	—	—	06VR-AN	06VR-BO	19.80	23.76	1,000
8	—	—	08VR-2R	08VR-AN	08VR-BO	27.72	31.68	500
10	10VR-6S	—	—	—	10VR-BO	35.64	39.60	500

Material and Surface finish, etc.

Contact: Copper alloy, tin-plated
Housing: PA


Note: 1. This product displays (LF)(SN) on a label.

2. A specified colored line is printed on the edge of each socket.


3. For flame retardant grade of resin material used, please refer to the "List of Registered Overseas Standards" on our website (listed in the "Technical Documents" column on the Product Information page).

Header

Top entry type



Side entry type



No. of circuits	Model No.		Dimensions (mm)		Q'ty/box	
	Top entry type	Side entry type	A	B	Top entry type	Side entry type
2	B2P-VR	B2PS-VR	3.96	7.92	1,000	250
3	B3P-VR	B3PS-VR	7.92	11.88	500	250
4	B4P-VR	B4PS-VR	11.88	15.84	250	250
5	B5P-VR	B5PS-VR	15.84	19.80	250	250
6	B6P-VR	B6PS-VR	19.80	23.76	250	100
8	B8P-VR	B8PS-VR	27.72	31.68	200	100
9	B9P-VR	—	31.68	35.64	100	—
10	B10P-VR	B10PS-VR	35.64	39.60	100	100

Material and Surface finish, etc.

Post: Copper alloy, tin-plated
Base housing: PA, natural

Note: 1. This product displays (LF)(SN) on a label.


2. In addition to VR headers, the VR socket can also be mated with VS headers and VH headers.

For further details, please refer to product catalogs and specifications or contact JST.


3. For flame retardant grade of resin material used, please refer to the "List of Registered Overseas Standards" on our website (listed in the "Technical Documents" column on the Product Information page).

Cover

For end connection



For daisy chain connection



No. of circuits	Model No.		Dimension A (mm)	Q'ty/box
	For end connection	For daisy chain connection		
2	—	VRC-02D	7.92	1,000
3	VRC-03E	VRC-03D	11.88	1,000
4	VRC-04E	VRC-04D	15.84	500
5	VRC-05E	—	19.80	500
6	VRC-06E	VRC-06D	23.76	500


Material and Surface finish, etc.

PVC, black


Note: 1. This product displays (LF) on a label.
 2. PVC (rigid form) material has lower common use heat-resistance and a lower softening point than PA material. Therefore, please take care when using the cover under high-temperature conditions.
 3. The use of the cover helps to prevent dust from adhering to the IDC contact area.
 4. For flame retardant grade of resin material used, please refer to the "List of Registered Overseas Standards" on our website (listed in the "Technical Documents" column on the Product Information page).

PC board layout and Assembly layout

Top entry type



Side entry type



Note: 1. The PC board layout figure shown is viewed from the connector mounting surface.


2. Tolerance for the PCB hole pitch shall be ± 0.05 and shall not accumulate.

3. Hole dimensions differ depending on the type of PCB and PCB drilling method.


The above dimensions are for reference only. Please contact JST for further details.

Model number allocation

Socket



Header



Cover

