


Product Overview

QM55011 is a hybrid, multi-band multi-chip RF front-end (RFFE) module supporting for NB-IoT1/2, Cat-M1/2 and NTN Non-Terrestrial-Networks application. The module supports LB (663MHz – 915MHz) and MB (1695MHz – 2010MHz). It has integrated harmonic rejection LPF, antenna switch and auxillary TX/RX path. QM55011 band select and bias are programmed through a Mobile Industry Processor Interface (MIPI).


Functional Block Diagram



Functional Block Diagram

Ordering Information

Part Number	Description
QM55011EVB	Evaluation Board Sample Kit
QM55011SB	5-Piece Sample Bag
QM55011SR	100-Piece 7inch Sample Reel
QM55011TR13	5000-Piece 13inch Reel



Package: Module, 24-Pin 3.00 x 3.00 x 0.60 mm

Key Features

- Integrated Switch Supports Multiple TX and RX paths
- MIPI RFFE Digital Control Interface
- Integrated harmonic reject LPF
- TRX switch ports support 2G power level
- Optimized use with DC/DC Converter Operation
- Average Power Tracking
- Optimized for Narrow-Band IoT1/2 and Cat-M1/2
- Programmable Bias Level Control
- 2.5V and 3.0V supplies

Applications

- Operating mid-bands: 1, 2, 3, 4, 25, 39, 65, 66, 70
- Operating low-bands: 5, 8, 12, 13, 14, 17, 18, 19, 20, 26, 27, 28, 71, 85
- Narrow-Band IoT1/2 and Cat-M1/2
- NTN bands

Handling Precautions

Parameter	Rating	Standard
ESD – Human Body Model (HBM)	Class 2	ESDA/JEDEC JS-001-2012
ESD – Charged Device Model (CDM)	Class C3	JEDEC JESD22-C101F
MSL – Moisture Sensitivity Level	MSL3	IPC/JEDEC J-STD-020



Caution!

ESD sensitive device

Solderability

Compatible with both lead-free (260 °C max. reflow temperature) and tin/lead (245 °C max. reflow temperature) soldering processes.

Package lead plating: Electrolytic plated Au over Ni

RoHS Compliance

This part is compliant with the 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment), as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Halogen Free (Chlorine, Bromine)
- Antimony Free
- TBBP-A (C₁₅H₁₂Br₄O₂) Free
- SVHC Free

Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: www.qorvo.com

Tel: 1-844-890-8163

Email: customer.support@qorvo.com

Important Notice

The information contained in this Data Sheet and any associated documents ("Data Sheet Information") is believed to be reliable; however, Qorvo makes no warranties regarding the Data Sheet Information and assumes no responsibility or liability whatsoever for the use of said information. All Data Sheet Information is subject to change without notice. Customers should obtain and verify the latest relevant Data Sheet Information before placing orders for Qorvo® products. Data Sheet Information or the use thereof does not grant, explicitly, implicitly or otherwise any rights or licenses to any third party with respect to patents or any other intellectual property whether with regard to such Data Sheet Information itself or anything described by such information.

DATA SHEET INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Without limiting the generality of the foregoing, Qorvo® products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death. Applications described in the Data Sheet Information are for illustrative purposes only. Customers are responsible for validating that a particular product described in the Data Sheet Information is suitable for use in a particular application.

© 2025 Qorvo US, Inc. All rights reserved. This document is subject to copyright laws in various jurisdictions worldwide and may not be reproduced or distributed, in whole or in part, without the express written consent of Qorvo US, Inc. | QORVO® is a registered trademark of Qorvo US, Inc.