


SURFACE MOUNT LED RED/GREEN, 0605 PACKAGE

BIVAR

SM0605BC-R/G


- ◆ Industry Standard 0605 Package
- ◆ RoHS Compliant
- ◆ 2 Chips in One Small Package and Footprint
- ◆ Water Clear Lens
- ◆ Wide Viewing Angle
- ◆ Ideal for Status Indication, Display, and Backlighting



Bivar now offers its smallest Bi-Color Surface Mount LED to date which gives designers the edge they need for smaller board designs that require multiple color outputs. Its miniature size makes it ideal for almost any application where board space is a priority without compromise to quality, and its long life and low power consumption are more than suitable for battery powered hand held devices and other portable products. This SM0605 LED is packaged in standard tape and reels for auto pick and place assemblies.

Part Number	Material	Emitted Color	Peak Wavelength λ_p (nm) TYP.	Lens Appearance	Luminous Intensity (mcd) TYP.	Viewing Angle
SM0605BC-R/G	AlGaInP	RED	645	Water Clear	90	120°
	AlGaInP	GREEN	575		45	

Outline Dimensions



Outline Drawings Notes:

1. All dimensions are in inches [millimeters].
2. Standard tolerance: ± 0.10 " unless otherwise noted.



Bivar reserves the right to make changes at any time without notice.

SURFACE MOUNT LED RED/GREEN, 0605 PACKAGE

BIVAR

Absolute Maximum Ratings

T_A = 25°C unless otherwise noted

Power Dissipation	Red - 78 mW Green - 78 mW
Continuous Forward Current	Red - 30 mA Green - 30 mA
Peak Forward Current ¹	100 mA
Reverse Voltage	5 V
Derating Linear From 25°C	0.4 mA/°C
Electrostatic Discharge (HBM)	2000 V
Operating Temperature Range	-40 ~ +85°C
Storage Temperature Range	-40 ~ +85°C
Lead Soldering Temperature ²	260°C

Notes: 1. ≤ 10% Duty Cycle, Pulse Width ≤ 0.1 msec. 2. Solder time less than 5 seconds at temperature extreme.

Electrical / Optical Characteristics


T_A = 25°C & I_F = 20 mA unless otherwise noted

Part Number	Emitted Color	Forward Voltage (V)			Recommend Forward Current (mA)			Dominant Wavelength (nm)			Luminous Intensity I _V (mcd)			Viewing Angle 2θ ½ (deg)
		MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	
SM0605BC-R/G	Red	1.8	2.1	2.6	/	20	/	623	631	640	90	115	145	120
	Green	1.95	2.1	2.6	/	20	/	570	574	576	36	45	57	





Bivar reserves the right to make changes at any time without notice.

Typical Electrical / Optical Characteristics (Red)

$T_A = 25^\circ\text{C}$ unless otherwise noted



Luminous Intensity Vs. Forward Current




Bivar reserves the right to make changes at any time without notice.


Typical Electrical / Optical Characteristics (Green)

$T_A = 25^\circ C$ unless otherwise noted


Forward Current Vs. Forward Voltage
 $T_A = 25^\circ C$




Luminous Intensity Vs. Forward Current
 $T_A = 25^\circ C$




Forward Current Derating Curve



Radiation Diagram



Spectrum Distribution




Bivar reserves the right to make changes at any time without notice.

SURFACE MOUNT LED RED/GREEN, 0605 PACKAGE

BIVAR

Tape and Reel Dimensions


Note: 4000 pcs / Reel



Outline Drawings Notes:

Outline Drawings Notes:

1. All dimensions are in inches [millimeters].
2. Standard tolerance: $\pm .010"$ unless otherwise noted.




Outline Drawings Notes:

1. All dimensions are in inches [millimeters].
2. Standard tolerance: $.xxx \pm .010"$, $.x \pm .1"$ unless otherwise noted.

Bivar reserves the right to make changes at any time without notice.

Packaging and Labeling Plan

Note: 1 Reel / Bag




Part No.	XXXX-XXX-XXX
Prod No.	XXXX-XXX-XXX
PO No.	XXXX
Lot No.	XXXXXXXXXX
Q'ty:	X.XXX PCS
Q.C.	XXX BIN
Date:	2017.XX.XX

Internal Quality Control Label



Bivar Standard Packaging Label

Recommended Soldering Conditions



Bivar reserves the right to make changes at any time without notice.