

Specification Sheet

Part Number: 110-95300



Unique levels of repeatability and accuracy.

High application speed and low maintenance.

Improved compressed air supply for faster tensioning piston movement.

Shorter processing time and greater volume of connecting tie application.

Ergonomic design.

Automatic ejection of cut-off cable tie end.

Ideally designed to apply stainless steel MBT-Series up to 16.0 mm width.

Pneumatic Mark 9 Stainless Steel Tie Tensioning and Cut-Off Tool, PL/GF, Black, 1/pkg

Article Number	110-95300
----------------	-----------

Type	MK9PSST
------	---------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	MK9PSST
---------------------	---------

Short Description	Pneumatic Mark 9 Stainless Steel Tie Tensioning and Cut-Off Tool, PL/GF, Black, 1/pkg
-------------------	---

Global Part Name	MK9PSST-PL-BK
Length L (Metric)	280
Width W (Metric)	55
Cable Ties	MBT-Series up to 16 mm width
Height H (Metric)	200
Cable Tie Width Max (Imperial)	0.63
Material	Plastic (PL)
Material Shortcut	PL
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1

Customs Number

8467195090

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)