

Specification Sheet

Part Number: MK9P

Tool made of heavy duty parts to ensure optimum performance in demanding environments.

Ideal for heavy-duty ties (T50-T250), clamp and button head ties.

Same ergonomic improvements as the MK7P.

Low weight, comfortable grip and easy trigger depression.

Very durable, with adjustable, easy to read tension settings.

Lock-out features available.

Comes with lower air attachment, and optional upper air attachment.



MK9 Pneumatic, Handle Air Supply Connection, Plastic Housing, 1/Pkg

Article Number 110-09101

Type MK9P

Color Black (BK)

Quantity Per pack

Product Description

The Mark 9 Pneumatic (MK9P) is constructed with heavy duty parts to ensure that it performs optimally in demanding environments. It is ideally designed to apply heavy-duty ties (T50-T250), clamp and button head ties. Like the MK7P, HellermannTyton's MK9P incorporates the next level of ergonomic improvement with its low weight, comfortable grip and easy trigger depression. Very durable, the pneumatic MK9P features adjustable, easy to read tension settings. Lock-out features are available. The MK9P is available with lower air attachment (standard) or can be ordered with an upper air attachment.

Short Description

MK9 Pneumatic, Handle Air Supply Connection, Plastic Housing, 1/Pkg

Global Part Name

MK9P-PA66GF30-BK

Length L (Metric)

280

Width W (Metric)

55

Cable Ties

T50 thru T250 Series CTT20 thru CTT175 Series EI-TY Series Button Head Series

Cycle Time

2 strokes per second

Height H (Metric)

200

Tension Setting Tools

Adjustable

Cable Tie Width Max (Imperial)

0.5

Power Supply

Dry or lubricated air

Material

Polyamide 6.6, glass fiber reinforced (PA66GF30%)

Material Shortcut

PA66GF30

UV Resistant (Yes/No)

No

Use Conditions

For Indoor and Outdoor Use

Reach Compliant (Article 33)

No

RoHS Compliant

Yes

Package Quantity (Imperial)

1

Package Quantity (Metric)

1

Customs Number

8467195090

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)