

Specification Sheet

Part Number: 111-00925

UV stabilized heavy duty cable ties contain an inhibitor which prolongs the life of the tie in UV exposures.

Inside serrations allow for strong grip on cables and wire bundles.

Head design provides high tensile strength with very low insertion force.

Bent tail ensures a quick and simple installation.



Heavy Duty Cable Tie, 22" Long, UL Rated, 250lb Tensile Strength, PA66UV, Black, 25/pkg

Article Number 111-00925

Type T250M

Color Black (BK)

Quantity Per bag

Product Description Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. The bent tail allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Heavy Duty Cable Tie, 22" Long, UL Rated, 250lb Tensile Strength, PA66UV, Black, 25/pkg

Global Part Name T250M-PA66UV-BK

Minimum Tensile Strength (Imperial) 250

Minimum Tensile Strength (Metric) 1115

Length L (Imperial) 22.3

Length L (Metric) 565.3

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.49

Width W (Metric) 12.4

Bundle Diameter Min (Imperial) 0.47

Bundle Diameter Min (Metric) 12.0

Bundle Diameter Max (Imperial) 5.91

Bundle Diameter Max (Metric) 150.0

Thickness T (Imperial) 0.07

Thickness T (Metric)	1.9
Material	Polyamide 6.6 UV-stabilized (PA66UV)
Material Shortcut	PA66UV
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)