

## Specification Sheet

Part Number: T50L7C2

Engineered and manufactured for maximum performance and quality

Made from 100% high-quality plastic to ensure efficient recycling

Inside serration for a strong grip onto bundles

Easy application either manually or with a processing tool



Cable Tie, 15" Long, UL Rated, 50lb Tensile Strength, PA66, Purple, 100/pkg

Article Number 111-05464

Type T50L

Color Purple (PE)

Quantity Per pack

**Product Description** T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description** Cable Tie, 15" Long, UL Rated, 50lb Tensile Strength, PA66, Purple, 100/pkg

Global Part Name T50L-PA66-VT

Minimum Tensile Strength (Imperial) 50

Minimum Tensile Strength (Metric) 225

Length L (Imperial) 15.3

Length L (Metric) 390.0

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.19

Width W (Metric) 4.8

Bundle Diameter Min (Imperial) 0.06

Bundle Diameter Min (Metric) 1.5

Bundle Diameter Max (Imperial) 4.33

Bundle Diameter Max (Metric) 110.0

Thickness T (Metric) 1.4

Cable Tie Head Length (Imperial)	0.28
Cable Tie Head Width (Imperial)	0.32
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Plenum Rating	AH-2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 62275
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes

UL Recognized (US and Canada) Yes

UL Listed (US) Yes

Package Quantity (Imperial) 100

Package Quantity (Metric) 100

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)