

Specification Sheet

Part Number: T150XL0X2



- Engineered and manufactured for maximum performance and quality.
- Made from 100% high-quality plastic to ensure efficient recycling.
- Inside serration for a strong grip onto bundles.
- Easy application either manually or with a tensioning tool.

Heavy Duty Cable Tie, 43" Long, UL Rated, 175lb Tensile Strength, PA66, Black, 25/pkg

Article Number	111-15500
Type	T150XL
Color	Black (BK)
Quantity Per	pack
Product Description	Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Heavy Duty Cable Tie, 43" Long, UL Rated, 175lb Tensile Strength, PA66, Black, 25/pkg

Global Part Name	T150XL-PA66-BK
------------------	----------------

Minimum Tensile Strength (Imperial)	175
-------------------------------------	-----

Minimum Tensile Strength (Metric)	780
-----------------------------------	-----

Length L (Imperial)	43.0
---------------------	------

Length L (Metric)	1095.0
-------------------	--------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.35
--------------------	------

Width W (Metric)	8.9
------------------	-----

Bundle Diameter Min (Imperial)	5.98
--------------------------------	------

Bundle Diameter Min (Metric)	152.0
------------------------------	-------

Bundle Diameter Max (Imperial)	12.99
--------------------------------	-------

Bundle Diameter Max (Metric)	330.0
------------------------------	-------

Thickness T (Imperial)	0.083
------------------------	-------

Thickness T (Metric)	2.1
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 62275 UL ANSI/UL 1565 UL ANSI/UL 746B
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)