

Specification Sheet

Part Number: 111-02390



Made from PVDF for high UV, chemical and thermal resistance.

Inside serrations deliver secure hold on cable and wire bundles.

Head design provides high tensile strength with low insertion force.

Cable Tie, 8" Long, 50lb Tensile Strength, PVDF, Gray, 100/pkg

Article Number	111-02390
Type	T50R
Color	Gray (GY)
Quantity Per	pack
Product Description	The PVDF cable tie is rated for 25 years' performance outdoors. It provides some of the highest UV, chemical and thermal resistance of any plastic resin. It functions just like our standard ties, simple and fast, streamlining installation and providing reliable performance.
Short Description	Cable Tie, 8" Long, 50lb Tensile Strength, PVDF, Gray, 100/pkg
Global Part Name	T50R-PVDF-GY

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	7.95
Length L (Metric)	202.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.31
Bundle Diameter Min (Metric)	8.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.47
Thickness T (Metric)	1.2

Cable Tie Head Length (Imperial)	0.29
Cable Tie Head Width (Imperial)	0.3
Material	Polyvinylidene Fluoride (PVDF)
Material Shortcut	PVDF
Flammability	UL 94 V-0
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +284°F (-40°C to +140°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100

Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)