

Specification Sheet

Part Number: T50L0HSM4



- Heat stabilized cable ties provide excellent resistance to high heat exposures.
- Inside serrations allow for strong grip on cables and wire bundles.
- Head design provides high tensile strength with very low insertion force.
- Bent tail ensures a quick and simple installation.

Article Number	111-05471
Type	T50L
Color	Black (BK)
Quantity Per	pack
Product Description	T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	High-Temp Cable Tie, 15" Long, UL Rated, 50lb Tensile Strength, PA66HS, Black, 1000/pkg
Global Part Name	T50L-PA66HS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	15.35
Length L (Metric)	390.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.19
Width W (Metric)	4.8
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	4.33
Bundle Diameter Max (Metric)	110.0
Thickness T (Metric)	1.4
Cable Tie Head Length (Imperial)	0.28

Cable Tie Head Width (Imperial)	0.32
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Plenum Rating	AH-2
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 62275
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000

Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)