

Specification Sheet

Part Number: T255R0HIRX2



- PA66HIRHSUV material is formulated to withstand extreme climate conditions and vibration.
- Inside serrations enhance strong grip on cables and wire bundles.
- Head design provides high tensile strength with low insertion force.
- Bent tail ensures a quick and simple installation.

Article Number	111-25400
Type	T255R
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton's T255 series heavy duty cable ties are ideal for bundles demanding a strong cable tie that may also require a higher impact resistance than the T250 series. These ties have a tensile strength of 250 pounds. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Heavy Duty Cable Tie, 20" Long, UL Rated, 250lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg

Global Part Name	T255R-PA66HIRHSUV-BK
------------------	----------------------

Minimum Tensile Strength (Imperial)	250
-------------------------------------	-----

Minimum Tensile Strength (Metric)	1115
-----------------------------------	------

Length L (Imperial)	20.0
---------------------	------

Length L (Metric)	508.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.50
--------------------	------

Width W (Metric)	12.7
------------------	------

Bundle Diameter Min (Imperial)	0.49
--------------------------------	------

Bundle Diameter Min (Metric)	12.5
------------------------------	------

Bundle Diameter Max (Imperial)	5.0
--------------------------------	-----

Bundle Diameter Max (Metric)	127.0
------------------------------	-------

Thickness T (Imperial)	0.07
------------------------	------

Thickness T (Metric)	1.8
Cable Tie Head Length (Imperial)	0.61
Cable Tie Head Width (Imperial)	0.80
Height H (Imperial)	0.37
Height H (Metric)	9.3
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes

UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)