

Specification Sheet

Part Number: RT255R0HIRX2



High impact, heat and UV stabilized releasable cable ties contain an impact modifier allowing greater flexibility and greater resistance to vibration.

Special design offers a release feature for quick and easy access to wire bundles.

Head design provides high tensile strength with very low insertion force even after repeated use.

Article Number	115-01300
----------------	-----------

Type	RT255R
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton heavy duty releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
---------------------	--

Short Description	Releasable Cable Tie, Release Tab, 20" Long, 250lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg
-------------------	---

Global Part Name	RT255R-PA66HIRHSUV-BK
------------------	-----------------------

Minimum Tensile Strength (Imperial)	250
-------------------------------------	-----

Minimum Tensile Strength (Metric)	1115
-----------------------------------	------

Length L (Imperial)	20.0
---------------------	------

Length L (Metric)	508.0
-------------------	-------

Fixation Method	Releasable Cable Tie
-----------------	----------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	Yes
--------------------	-----

Width W (Imperial)	0.5
--------------------	-----

Width W (Metric)	12.6
------------------	------

Bundle Diameter Min (Imperial)	0.98
--------------------------------	------

Bundle Diameter Min (Metric)	25.0
------------------------------	------

Bundle Diameter Max (Imperial)	5
--------------------------------	---

Bundle Diameter Max (Metric)	127.0
------------------------------	-------

Cable Tie Width Max (Imperial)	0.49
--------------------------------	------

Cable Tie Width Max (Metric)	12.5
------------------------------	------

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)