

## Specification Sheet

Part Number: IT18FL9C2



Identification plate feature allows bundles to be easily marked and identified.

Wire and cable harnesses can be secured and identified using just one product, which saves time.

Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.

Article Number 111-81919

Type IT18FL

Color Natural (NA)

Quantity Per pack

Product Description Identification cable ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.

Short Description Identification Tie, 4.3" Long, 18lb Tensile Strength, PA66, Natural, 100/pkg

Global Part Name IT18FL-PA66-NA

Minimum Tensile Strength (Imperial)	18
Minimum Tensile Strength (Metric)	80
Length L (Imperial)	4.3
Length L (Metric)	110.0
Fixation Method	None
Identification Plate Position	stands of bundle
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.81
Width W (Metric)	20.5
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	0.75
Bundle Diameter Max (Metric)	19.0
Height H (Imperial)	0.35

Height H (Metric)	9.0
Outside Diameter Max (Imperial)	0.75
Outside Diameter Min (Metric)	1.50
Outside Diameter Min (Imperial)	0.059
Outside Diameter Max (Metric)	19.00
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL   ANSI/UL 62275 UL   CSA -C22.2 no. 62275
UL Recognized (US)	Yes

UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988
Weight (Metric)	0.3

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)