

Specification Sheet

Part Number: 151-00464

HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.



Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.

An assortment of Connector Cips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Connector Clip, with Edge Clip, Panel Thickness 1.0-3.0mm, PA66HIRHS, Black, 1000/pkg

Article Number 151-00464

Type EC6mod

Color Black (BK)

Quantity Per pack

Product Description Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description Connector Clip, with Edge Clip, Panel Thickness 1.0-3.0mm, PA66HIRHS, Black, 1000/pkg

Global Part Name

EC6mod-PA66HIRHS-BK

Length L (Imperial) 0.87

Length L (Metric) 22.0

Fixation Method Edge Clip

Width W (Imperial) 0.4

Width W (Metric) 10.4

Height H (Imperial) 6.0

Height H (Metric) 15.5

Panel Thickness Min (Imperial) 0.04

Panel Thickness Max (Imperial) 0.12

Panel Thickness Min (Metric) 1.0

Panel Thickness Max (Metric) 3.0

Material Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut PA66HIRHS

Flammability UL 94 HB

UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
RoHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)