

## Specification Sheet

Part Number: 151-00786



HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.

An assortment of Connector Clips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Connector Clip with Round Fir Tree, 0.7-11.0 mm Panel Thick., 6.0 - 6.7 mm Hole Dia, PA66HIRHS, Black, 5000/box

|                |           |
|----------------|-----------|
| Article Number | 151-00786 |
|----------------|-----------|

|      |          |
|------|----------|
| Type | CCFT6XLG |
|------|----------|

|       |            |
|-------|------------|
| Color | Black (BK) |
|-------|------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                                                                                                           |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly. |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                                                                 |
|-------------------|-----------------------------------------------------------------------------------------------------------------|
| Short Description | Connector Clip with Round Fir Tree, 0.7-11.0 mm Panel Thick., 6.0 - 6.7 mm Hole Dia, PA66HIRHS, Black, 5000/box |
|-------------------|-----------------------------------------------------------------------------------------------------------------|

|                  |                       |
|------------------|-----------------------|
| Global Part Name | CCFT6XLG-PA66HIRHS-BK |
|------------------|-----------------------|

|                     |     |
|---------------------|-----|
| Length L (Imperial) | 0.9 |
|---------------------|-----|

|                   |      |
|-------------------|------|
| Length L (Metric) | 23.0 |
|-------------------|------|

|                 |                          |
|-----------------|--------------------------|
| Fixation Method | Fir tree for round holes |
|-----------------|--------------------------|

|                  |      |
|------------------|------|
| Width W (Metric) | 16.1 |
|------------------|------|

|                     |      |
|---------------------|------|
| Height H (Imperial) | 0.95 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Height H (Metric) | 24.2 |
|-------------------|------|

|                                |      |
|--------------------------------|------|
| Panel Thickness Min (Imperial) | 0.03 |
|--------------------------------|------|

|                                |      |
|--------------------------------|------|
| Panel Thickness Max (Imperial) | 0.43 |
|--------------------------------|------|

|                              |     |
|------------------------------|-----|
| Panel Thickness Min (Metric) | 0.7 |
|------------------------------|-----|

|                              |      |
|------------------------------|------|
| Panel Thickness Max (Metric) | 11.0 |
|------------------------------|------|

|                                     |               |
|-------------------------------------|---------------|
| Mounting Hole Diameter D (Imperial) | 0.24 - 0.26 " |
|-------------------------------------|---------------|

|                                   |              |
|-----------------------------------|--------------|
| Mounting Hole Diameter D (Metric) | 6.0 - 6.7 mm |
|-----------------------------------|--------------|

|                                         |      |
|-----------------------------------------|------|
| Mounting Hole Diameter D Min (Imperial) | 0.24 |
|-----------------------------------------|------|

|                                         |      |
|-----------------------------------------|------|
| Mounting Hole Diameter D Max (Imperial) | 0.26 |
|-----------------------------------------|------|

|                                       |     |
|---------------------------------------|-----|
| Mounting Hole Diameter D Max (Metric) | 6.7 |
|---------------------------------------|-----|

|                              |                                                                  |
|------------------------------|------------------------------------------------------------------|
| Material                     | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| Material Shortcut            | PA66HIRHS                                                        |
| Flammability                 | UL 94 HB                                                         |
| UV Resistant (Yes/No)        | No                                                               |
| Use Conditions               | For Indoor and Outdoor Use                                       |
| Operating Temperature        | -40°F to +221°F (-40°C to +105°C)                                |
| Reach Compliant (Article 33) | Yes                                                              |
| ROHS Compliant               | Yes                                                              |
| Package Quantity (Imperial)  | 5000                                                             |
| Package Quantity (Metric)    | 5000                                                             |
| Customs Number               | 3926909988                                                       |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)