

Specification Sheet

Part Number: 151-04683



Simple to instal

Excellent security, particularly in areas of high vibration

Maximum surface area with adhesive to achieve high pull-off force

4-way entry for cable tie for quicker and more flexible installation

Article Number

151-04683

Type

WRMB12A

Color

White (WH)

Quantity Per

bag

Product Description

Adhesive Fastened Mounting Bases are used with 18 through 150 lb. cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by securing two or four screws. The four-way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles.

Short Description

WireRail Rubber Adhesive Mounting Base, 12 x 0.75", Use with T18-T120 Cable Ties or GT.375-GT.75 Grip Ties, PA66HS, White, 50/bag

Global Part Name	WRMB12A-PA66HS-WH
Length L (Imperial)	12.0
Length L (Metric)	304.8
Fixation Method	Screw Mounting and Adhesive
Width W (Imperial)	0.86
Width W (Metric)	21.9
Height H (Imperial)	0.33
Height H (Metric)	8.5
Mounting Hole Diameter D (Imperial)	0.19 "
Mounting Hole Diameter D (Metric)	4.8 mm
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V-2 (excluding adhesive)
Halogen Free	Yes

Adhesive Operating Temperature	0°F to +150°F (-18 °C to +66 °C)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)