

Specification Sheet

Part Number: 150-74890



Fir tree design can be used with a wide variety of applications.

Disc' on the top of the fir tree covers the hole and minimizes the ingress of water and dirt.

Friction tab inside of fir tree allows tie to sit in mount without falling out prior to installation.

2-Piece Cable Tie with Fir Tree Mount, 6.0" Long, 0.23 - 0.24" Mounting Hole, PA66HS, Black, 500/pkg

Article Number	150-74890
----------------	-----------

Type	T30RFT6D10
------	------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton's fir tree mounts provide a secure grip in a mounting hole and protect against dirt and other impurities. The mount can slide along the strap of the cable tie for proper orientation. The fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.
---------------------	---

Short Description	2-Piece Cable Tie with Fir Tree Mount, 6.0" Long, 0.23 - 0.24" Mounting Hole, PA66HS, Black, 500/pkg
-------------------	--

Global Part Name	T30RFT6D10-PA66HS/PA66HIRHS-BK
------------------	--------------------------------

Minimum Tensile Strength (Imperial)	30
-------------------------------------	----

Minimum Tensile Strength (Metric)	135
-----------------------------------	-----

Length L (Imperial)	6.0
---------------------	-----

Length L (Metric)	150
-------------------	-----

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.14
--------------------	------

Width W (Metric)	3.5
------------------	-----

Bundle Diameter Max (Imperial)	1.26
--------------------------------	------

Bundle Diameter Max (Metric)	32.0
------------------------------	------

Height H (Imperial)	0.04
---------------------	------

Height H (Metric)	1.1
-------------------	-----

Panel Thickness Min (Imperial)	0.03
--------------------------------	------

Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	0.8
Panel Thickness Max (Metric)	4.3
Mounting Hole Diameter D (Imperial)	0.23 - 0.24 "
Mounting Hole Diameter D (Metric)	5.8 - 6.2 mm
Mounting Hole Diameter D Min (Imperial)	0.23
Mounting Hole Diameter D Max (Imperial)	0.24
Mounting Hole Diameter D Max (Metric)	6.2
Disc Diameter (Metric)	9.8
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Foot Part Material	PA66HIRHS
Material Shortcut	PA66HIRHS PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB

UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)