

## Specification Sheet

Part Number: 151-00077



Clip can be installed by hand – no need for hardware or tools.

Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

Standoff Bundling Clip, 2.0" Long, 0.03 - 0.06" Panel Thickness, PA66HS, Black, 100/pkg

Article Number 151-00077

Type CH20D6

Color Black (BK)

Quantity Per pack

Product Description Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as stand-off and stud mount versions.

Short Description Standoff Bundling Clip, 2.0" Long, 0.03 - 0.06" Panel Thickness, PA66HS, Black, 100/pkg

Global Part Name

CH20D6-PA66HS-BK

Length L (Imperial) 2.0

Length L (Metric) 50.0

Offset Length (Imperial) 0.79

Offset Length (Metric) 20.0

Fixation Method Arrowhead

Height H (Imperial) 0.3

Height H (Metric) 7.62

Panel Thickness Min (Imperial) 0.02

Panel Thickness Max (Imperial) 0.06

Panel Thickness Min (Metric) 0.6

Panel Thickness Max (Metric) 1.4

Mounting Hole Diameter D (Imperial) 0.25 - 0.28 "

Mounting Hole Diameter D (Metric) 6.4 - 7.0 mm

Mounting Hole Diameter D Min (Imperial) 0.25

Mounting Hole Diameter D Max (Imperial) 0.28

Mounting Hole Diameter D Max (Metric) 7.0

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability UL 94 V-2

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 100

Package Quantity (Metric) 100

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

