

Specification Sheet

Part Number: 151-04349

Modular connector clip design eliminates the need for investment in expensive tools for TPE products or upsetting of tubes and pipes.

Compact size for mounting in tight spaces.

Fine-pitch ratchet provides controlled grip for a range of pipe sizes with one part.

Fully enclosed clamp prevents slip, crush and fallout under vacuum.

Release latch with simple twist of screwdriver.



Article Number	151-04349
Type	ROC18.5-22.5SLOT17
Color	Black (BK)
Quantity Per	carton
Product Description	The Ratchet O-Clamp is designed for tight spaces, maintaining a low profile while providing an adjustable closure for a range of bundle sizes. HellermannTyton's connector clips provide a single method to mount connectors to various surfaces in a variety of applications. Slot can be paired with any HellermannTyton standard USCAR17 connector clip mount.

Short Description	Ratchet O-Clamp, 0.73 - 0.88" Bundle Dia, 17 mm Connector Clip Slot, PA66HIRHSUV, BK, 1000/ctn
Global Part Name	ROC18.5-22.5SLOT17-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	100
Minimum Tensile Strength (Metric)	445
Length L (Imperial)	2.29
Length L (Metric)	58.1
Fixation Method	Connector Clip
Width W (Imperial)	1.00
Width W (Metric)	25.5
Bundle Diameter Min (Imperial)	0.73
Bundle Diameter Min (Metric)	18.5
Bundle Diameter Max (Imperial)	0.88
Bundle Diameter Max (Metric)	22.5
Height H (Imperial)	1.93
Height H (Metric)	49.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)