


Specification Sheet

Part Number: MB50C2



Compact size fits most mounting applications.

Simple to install with a screw or rivet.

Single hole attachment with two-way entry for cable tie.

Screw Mount Cable Tie Base, 1.49 x 1.49", 0.35" Max Tie Width, 0.19" Hole Dia, PA66, Black, 100/pkg

Article Number	151-28500
----------------	-----------

Type	MB5
------	-----

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	These cable tie mounts are compact in size. They are designed for simple yet robust installation. They pair with a cable tie for mounting applications including telecom equipment, switchgear and control cabinets.
---------------------	--

Short Description	Screw Mount Cable Tie Base, 1.49 x 1.49", 0.35" Max Tie Width, 0.19" Hole Dia, PA66, Black, 100/pkg
-------------------	---

Global Part Name	MB5-PA66-BK
------------------	-------------

Length L (Imperial)	1.49
Length L (Metric)	37.7
Fixation Method	Screw Mount
Width W (Imperial)	1.49
Width W (Metric)	37.7
Cable Ties	T18 - T150
Height H (Imperial)	.25
Height H (Metric)	6.20
Cable Tie Width Max (Imperial)	0.35
Cable Tie Width Max (Metric)	8.9
Mounting Hole Diameter D (Imperial)	0.19 "
Mounting Hole Diameter D (Metric)	4.8 mm
Mounting Hole Diameter D Max (Metric)	4.8
Mounting Hole Centers (Imperial)	1.0
Material	Polyamide 6.6 (PA66)

Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
BABA Compliant	YES
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Privacy Policy](#)

[Cookie Policy](#)

[Terms and Conditions](#)