

Specification Sheet

Part Number: 155-30902



Clip can be installed by hand – no need for hardware or tools.

Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

Standoff Bundling Clip, 2.2" Long, Panel Thickness .02 - .03", PA66HIRHS, Black, 500/box

Article Number	155-30902
----------------	-----------

Type	SOC4MFT6
------	----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using bundle or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.
---------------------	--

Short Description	Standoff Bundling Clip, 2.2" Long, Panel Thickness .02 - .03", PA66HIRHS, Black, 500/box
-------------------	--

Global Part Name	SOC4MFT6-PA66HIRHS-BK
------------------	-----------------------

Length L (Imperial)	2.2
---------------------	-----

Length L (Metric)	55.0
-------------------	------

Offset Length (Imperial)	0.79
--------------------------	------

Offset Length (Metric)	20.0
------------------------	------

Fixation Method	Fir Tree
-----------------	----------

Width W (Metric)	20.0
------------------	------

Height H (Imperial)	0.54
---------------------	------

Height H (Metric)	13.7
-------------------	------

Panel Thickness Min (Imperial)	0.03
--------------------------------	------

Panel Thickness Max (Imperial)	0.20
--------------------------------	------

Panel Thickness Min (Metric)	0.7
------------------------------	-----

Panel Thickness Max (Metric)	5.1
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.26 - 0.28 "
-------------------------------------	---------------

Mounting Hole Diameter D (Metric)	6.5 - 7.0 mm
-----------------------------------	--------------

Mounting Hole Diameter D Min (Imperial)	0.26
---	------

Mounting Hole Diameter D Max (Imperial) 0.28

Mounting Hole Diameter D Max (Metric) 7.0

Material Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut PA66HIRHS

Flammability UL 94 HB

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 500

Package Quantity (Metric) 500

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)