

## Specification Sheet

Part Number: 156-03939

Friction tab inside the fir tree keeps tie in mount without falling out prior to installation.

Suitable for use within threaded holes

DOP versions for oval holes feature anti-twist protection.

Cable tie is outside serrated to reduce bundle chafing.

Low profile cable tie helps bundle wires neatly to accommodate wire harnesses with smaller diameters.

Low profile head won't snag on surrounding parts and wires.



2-Piece Low-Profile Cable Tie with Oval Fir Tree, 7.7" L, 6.2 x 12.2 mm; 6.5 x 12.5 mm; 6.5 x 13.0 mm or 7.0 x 12.0 mm Mounting Hole, PA66HS/PA66HIRHSUV, Black, 2000/ctn

Article Number 156-03939

Type LPT50RSADFTOVAL-SET

Color Black (BK)

Quantity Per pack

## Product Description

HellermannTyton's Two-Piece Fir Tree Cable Ties offer a simple and versatile method of bundling and mounting cables. The fir tree is easy to insert into pre-punched holes in panels or threaded blind holes and offers a secure hold. Two-piece design enables the tie head to be orientated in the required position to ease assembly. The disc above the fir tree covers the hole and minimizes the ingress of water and debris. Fir tree mounts provide a secure grip in a mounting hole and are designed to provide a low insertion force and high extraction force. The low profile cable tie features a compact, contoured head designed to use less space in confined areas and reduce protrusions that might otherwise interfere with or damage adjacent wire insulation and hoses. Outside serration provides a smooth inside surface to further minimize indentation or damage to soft bundles while offering high tensile strength and low insertion force. This mount is sold as an assembly with the cable tie.

## Short Description

2-Piece Low-Profile Cable Tie with Oval Fir Tree, 7.7" L, 6.2 x 12.2 mm; 6.5 x 12.5 mm; 6.5 x 13.0 mm or 7.0 x 12.0 mm Mounting Hole, PA66HS/PA66HIRHSUV, Black, 2000/ctn

## Global Part Name

LPT50RSADFTOVAL-SET-PA66HS/PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 50

Minimum Tensile Strength (Metric) 225

Length L (Imperial) 7.7

Length L (Metric) 194.6

Fixation Method Fir Tree for oval holes

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.24
Bundle Diameter Min (Metric)	6.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.787
Height H (Metric)	20.0
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.08
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.26 x 0.51 " 0.26 x 0.49 " 0.24 x 0.48 " 0.28 x 0.47 "
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm 6.5 x 13.0 mm 6.5 x 12.5 mm 7.0 x 12.0 mm

Mounting Hole Diameter D Min (Imperial) 0.24

Mounting Hole Diameter D Max (Imperial) 0.51

Mounting Hole Diameter D Max (Metric) 7.0

Material Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Foot Part Material PA66HIRHSUV

Material Shortcut PA66HS PA66HIRHSUV

Material Cable Tie Polyamide 6.6 heat stabilized (PA66HS)

UV Resistant (Yes/No) Yes

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 2000

Package Quantity (Metric) 2000

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)