

Specification Sheet

Part Number: 156-03945

Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

Two-piece assembly allows the mount to slide along the strap, ensuring proper orientation.

Cable tie is outside serrated to reduce bundle chafing.

Low profile cable tie helps bundle wires neatly to accommodate wire harnesses with smaller diameters.

Low profile head won't snag on surrounding parts and wires.



2-Piece Low-Profile Cable Tie with EC4A Edge Clip, 7.7" L, 1 - 3mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/bg

Article Number 156-03945

Type LPT50REC4A

Color Black (BK)

Quantity Per pack

Product Description

HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place. EC4A orientation allows cables to run parallel to the edge. The lowprofile cable tie features a compact, contoured head that uses less space in confined areas and reduces protrusions that might otherwise interfere with or damage adjacent wire insulation and hoses. The outside serration provides a smooth inside surface to further minimize indentation or damage to soft bundles while offering high tensile strength and low insertion force. The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature extremes. Edge clips are widely used for attaching cables and wires within automotive, trucking, heavy equipment, solar panel, wind power and white goods equipment manufacturing.

Short Description

2-Piece Low-Profile Cable Tie with EC4A Edge Clip, 7.7" L, 1 - 3mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/bg

Global Part Name

LPT50REC4A-PA66HS/PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

50

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

7.7

Length L (Metric)

194.6

Fixation Method

Edge Clip

Identification Plate Position

none

Releasable Closure

No

Width W (Imperial)

0.18

Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.2
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Height H (Imperial)	0.05
Height H (Metric)	1.20
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.08
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0

Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Foot Part Material	PA66HIRHSUV
Material Shortcut	PA66HS PA66HIRHSUV
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C) -40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988