


Specification Sheet

Part Number: 157-00119

Offset design allows bundles to sit off of mounting points to avoid friction against surrounding areas.

Fir tree gives 3 to 1 extraction versus insertion force making them strong and easy to install.

Friction tab inside of fir tree allows tie to sit in mount without falling out prior to installation.



1-Piece Cable Tie with Offset Fir Tree with Disc, 25 mm Offset, 9.1"L, 6.1 - 7.0 mm or 6.35 mm (hexagonal) Hole, PA66HIRHS, Gray, 3000/ctn

Article Number	157-00119
Type	T50ROSFT6SO25A
Color	Gray (GY)
Quantity Per	pack

Product Description	Offset cable ties route and position bundles away from a mounting hole. Rigid offset bar eliminates potential bending of wire or cables once installed. Multiple offset distances and fir tree sizes cover the majority of industry offset applications. The tie strap's outside serration design provides a smooth surface to protect soft bundles. HellermannTyton's one-piece mounting ties offer a complete solution by both bundling and mounting. Their ideal combination of high-specification materials and superior design suit the needs of complex applications.
---------------------	---

Short Description	1-Piece Cable Tie with Offset Fir Tree with Disc, 25 mm Offset, 9.1"L, 6.1 - 7.0 mm or 6.35 mm (hexagonal) Hole, PA66HIRHS, Gray, 3000/ctn
Global Part Name	T50ROSFT6SO25A-PA66HIRHS-GY
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	9.1
Length L (Metric)	230.0
Offset Length (Imperial)	0.98
Offset Length (Metric)	25.0
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Width W (Imperial)	0.20
Width W (Metric)	5.1
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0

Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.89
Height H (Metric)	21.20
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.26
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.65
Mounting Hole Diameter D (Imperial)	0.25 " (HEXAGONAL) 0.24 - 0.28 "
Mounting Hole Diameter D (Metric)	6.1 - 7.0 mm 6.35 mm (hexagonal)
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.0
Disc Diameter (Metric)	19.0
Disc Diameter (Imperial)	0.75

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com