

Specification Sheet

Part Number: 157-00151



Head allows for a 0.2" lateral adjustment on stud during installation.

Quick and easy installation ideal for manufacturing environment.

1-Piece Cable Tie with Oval Stud Mount, Designed for 5.0 - 6.0 mm stud, 6.0" Long, PA66HS, Gray, 1000/bg

Article Number	157-00151
----------------	-----------

Type	T50SOSSB5-High-E-C-CC
------	-----------------------

Color	Gray (GY)
-------	-----------

Quantity Per	pack
--------------	------

Product Description	Oval Shaped Stud Mount's special design allows for a 0.2" (5.5mm) lateral adjustment, allowing for any misalignment of the stud or incorrect position of the tie on the cables. The "soft push" mount allows it to be installed onto a weld stud without the use of any tools.
---------------------	--

Short Description	1-Piece Cable Tie with Oval Stud Mount, Designed for 5.0 - 6.0 mm stud, 6.0" Long, PA66HS, Gray, 1000/bg
-------------------	--

Global Part Name	T50SOSSB5-High-E-C-CC-PA66HS-GY
------------------	---------------------------------

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	222.4
Length L (Imperial)	6.57
Length L (Metric)	167.0
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.20
Width W (Metric)	5.0
Bundle Diameter Min (Imperial)	0.04
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Stud Length Max (Imperial)	0.56

Stud Length Max (Metric)	14.2
Stud Diameter (Metric)	5.0 mm 6.0 mm
Stud Diameter (Imperial)	0.20
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)