

Specification Sheet


Part Number: 161-64417

Unique open design for easy branch-offs at any point along the harness.

Overwrap formation provides abrasion protection and accommodates multiple bundle configurations.

Flexible construction and design eliminates pinch points and minimizes bending fatigue, making it ideal for applications involving movement and vibration.

Split shape allows for future access without disassembly.



Helawrap, HWPP25, Convenience Pack, 1" (25mm) Dia, PP, White, 10ft/pkg

Article Number 161-64417

Type HWPP25

Color White (WH)

Quantity Per pack

Product Description

The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.

Short Description	Helawrap, HWPP25, Convenience Pack, 1" (25mm) Dia, PP, White, 10ft/pkg
Global Part Name	HWPP25-PP-WH
Length L (Imperial)	10.0
Length L (Metric)	3.05
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.91
Bundle Diameter Min (Metric)	23.11
Bundle Diameter Max (Imperial)	1.06
Bundle Diameter Max (Metric)	26.92
Diameter D (Imperial)	1.0
Diameter D (Metric)	25.40
Nominal Diameter (Imperial)	1
Nominal Diameter (Metric)	25.0
Wall Thickness WT (Imperial)	0.041
Wall Thickness WT (Metric)	1.05

Material	Polypropylene (PP)
Material Shortcut	PP
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-76°F to +230°F (-60°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	EDAG-LAB ECE R-118-03 Abschnitt 6 / Annex 6
Package Quantity (Imperial)	10.0
Package Quantity (Metric)	3.05
Customs Number	3926909988