

Specification Sheet

Part Number: 167-00203

Living hinge allows harness serviceability and reduces assembly time.

Internal ribs affix to exterior of tubing which prevents slipping during tension or movement.

Snap-on connection makes installations quick and easy and increases efficiencies in harness assembly.

Junction point outlets offer additional areas to branch off wires and prevents wires from sliding or accidental removal from tubing.

Improves aesthetics of assembled wire harness.

No tools required to disassemble.



Hinged Convoluted Loom Tubing Breakout Fitting, L- 0.5" x R- 0.5", PP, Black, 1100/pkg

Article Number 167-00203

Type CTHC-B55

Color Black (BK)

Quantity Per pack

Product Description

Convoluted Loom fittings are single piece hinged connectors that simply snap-on over slit and unslit loom tubing to secure wire branchouts or, connect different tubing diameters. The unique wrap around design makes installation easier and more efficient, while the unique junction points make easy branchouts that keep wires from sliding out of the tubing and eliminates need for secondary taping operation. The polypropylene material creates a sleek assembly and improves the appearance of the entire wiring assembly.

Short Description

Hinged Convoluted Loom Tubing Breakout Fitting, L- 0.5" x R- 0.5", PP, Black, 1100/pkg

Global Part Name

CTHC-B55-PP-BK

Variant

Fittings

Inner Diameter D (Imperial)

0.50

Inner Diameter D (Metric)

12.7

Diameter D (Imperial)

0.50

Diameter D (Metric)

12.7

Nominal Diameter (Imperial)

0.50

Nominal Diameter (Metric)

12.7

Material

Polypropylene (PP)

Material Shortcut

PP

Flammability

UL 94 HB

Halogen Free

Yes

UV Resistant (Yes/No)

No

Use Conditions

For Indoor Use Only

Operating Temperature

-4°F to +194°F (-20°C to +90°C)

Reach Compliant (Article 33)

No

ROHS Compliant

Yes

Package Quantity (Imperial)

1100

Package Quantity (Metric)

1100

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)