

Specification Sheet

Part Number: SNP1.5GHS0M4

Installation and removal can be five times faster

than conventional clamps

Heat stabilized material is suitable for high temperature applications.

Completely reusable

Will not rust or corrode

Safety engineered.

No protruding band or cluster.

Can be installed with hose in place



One-hand installation for tight places.

Snapper Hose Clamp, 0.32 - 0.35" Bundle Diameter, PA66GF13, Black, 1000/pkg

Article Number 190-00035

Type SNP1.5

Color	Black (BK)
Quantity Per	pack
Product Description	<p>The Snapper Hose Clamp features a ratchet-style closure for reduced assembly time. It can be added after connection of the hose. Release by sliding the ratchet ends apart. Snappers can be used in under-hood applications and are stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils and greases. They are manufactured in black PA66 glass filled, impact modified, heat stabilized material. Custom design and color options are available based upon application and volume requirements.</p>
Short Description	Snapper Hose Clamp, 0.32 - 0.35" Bundle Diameter, PA66GF13, Black, 1000/pkg
Global Part Name	SNP1.5-PA66GF13-BK
Fixation Method	Plug-in mounting
Variant	Closed
Bundle Diameter Min (Imperial)	0.31
Bundle Diameter Min (Metric)	8.0
Bundle Diameter Max (Imperial)	0.35
Bundle Diameter Max (Metric)	8.9
Wall Thickness WT (Imperial)	.055
Wall Thickness WT (Metric)	1.414

Material	Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13%)
Material Shortcut	PA66GF13
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)