








Isometric view



Isometric view
Rotated

Clip rotates
360 degrees



Stud mount

MOC22M

Reference:

Performance requirements at dry as molded:

1. Stud mount push on force: 45 newtons (10 lbf) max on each applicable stud size.
2. Stud mount pull off force: 110 newtons (25 lbf) min on each applicable stud size.

Notes:

1. Material: See chart
2. Material color: See chart
3. Maximum percent regrind permissible: 25%
4. Max allowable flash to be: 0.25mm
5. Max allowable mismatch to be: 0.1mm
6. Applicable stud size:

- A. M5 x 0.8
- B. T5
- C. M6 x 1
- D. T6

* Recommended sizes may differ depending on the application, product requirements, and materials used.

** Rotational orientation of clips upon delivery is not controlled

*** Patent: US D822,476 S, EU 003864313, CN 304373914 S

01.2

Diameter Range*		
Harness	Hose	Hard Pipe/Tube
20.0mm-24.0mm	20.0mm-24.0mm	22.0mm-25.0mm

Global Part Description	MOC22M***			Stud Mount		
	Drawing	Material	Color	Drawing	Material	Color
SMF2MOC22M-PA66HIRHSUV-BK	16-0323-002-CSU	PA66HIRHSUV	Black	19-0239-001-CSU	PA66HIRHSUV	Black

Revision Level			Revision Record			The copyright of this drawing is reserved by HellermannTyton.		Drawn		Date (YYYY/MM/DD)								
Drawing	State		Part	ECN 310016		All drawing revisions are stored in CAD PDM database		Klos		2021/09/22		Title		Scale 1:1				
01.2	Design Release		-		Approved			Date (YYYY/MM/DD)										
Changed		Date (YYYY/MM/DD)			Units mm			HellermannTyton		Karabon		2021/09/22		MOC22M coupled with a M5/M6 stud mount		Global Project Number 19-1676		
Rohde		2023/06/15																
Approved		Date (YYYY/MM/DD)										Drawing-No 19-1676-001-CSU		Format A3				
Haftarski		2023/06/15												Sheet 1 / 1				