

Specification Sheet

Part Number: 309-20953

Quick and easy shrinking TF21 tubing is widely used for insulating, mechanical protection, strain relief, marking, and bundling.

The excellent balance of electrical, mechanical and chemical properties meet and exceed industrial standards.

TF21 is UL-224 listed and available in a wide range of sizes and colors.



Heat Shrink Tubing, Bulk Reel, 2:1 Shrink Ratio, 3/8", 9.5/4.8 Dia, PO, Orange, 164.0 ft/reel

Article Number 309-20953

Type TF21-9.5/4.8

Color Orange (OG), High Voltage (HV)

Quantity Per pack

Product Description TF21 is a highly flexible thin wall heat shrink tubing with a 2-to-1 shrink ratio and excellent flame retardant properties. In addition to providing insulation and abrasion protection for wires and cables, the polyolefin material also offers resistance to oils, solvents and chemicals. TF21 is UL Recognized with a UL 224 VW-1 flame rating.

Short Description Heat Shrink Tubing, Bulk Reel, 2:1 Shrink Ratio, 3/8", 9.5/4.8 Dia, PO, Orange, 164.0 ft/reel

Global Part Name

TF21-9.5/4.8-PO-X-OG

Variant

Thin-Wall

Wall Thickness WT (Imperial)

0.025

Wall Thickness WT (Metric)

0.64

Material

Polyolefin, cross-linked (PO-X)

Material Shortcut

PO-X

Flammability

ASTM D876

Halogen Free

No

UV Resistant (Yes/No)

No

Use Conditions

For Indoor Use Only

Operating Temperature

-67°F to +275°F (-55°C to +135°C)

Reach Compliant (Article 33)

Yes

ROHS Compliant

Yes

Certification/Specification

JAR/FAR 25.853 UL | ANSI/UL 224

UL Recognized (US)

Yes

Package Quantity (Imperial) 164.0

Package Quantity (Metric) 50

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)