

Specification Sheet

Part Number: 309-21903

Quick and easy shrinking TF21 tubing is widely used for insulating, mechanical protection, strain relief, marking, and bundling.

The excellent balance of electrical, mechanical and chemical properties meet and exceed industrial standards.

TF21 is UL-224 listed and available in a wide range of sizes and colors.



Heat Shrink Tubing, Bulk Reel, 2:1 Shrink Ratio, 3/4", 19.1/9.5 Dia, PO, Orange, 82.0 ft/reel

Article Number 309-21903

Type TF21-19.1/9.5

Color Orange (OG), High Voltage (HV)

Quantity Per pack

Product Description TF21 is a highly flexible thin wall heat shrink tubing with a 2-to-1 shrink ratio and excellent flame retardant properties. In addition to providing insulation and abrasion protection for wires and cables, the polyolefin material also offers resistance to oils, solvents and chemicals. TF21 is UL Recognized with a UL 224 VW-1 flame rating.

Short Description Heat Shrink Tubing, Bulk Reel, 2:1 Shrink Ratio, 3/4", 19.1/9.5 Dia, PO, Orange, 82.0 ft/reel

Global Part Name

TF21-19.1/9.5-PO-X-OG

Variant

Thin-Wall

Bundle Diameter Min (Imperial)

0.37

Bundle Diameter Min (Metric)

9.5

Bundle Diameter Max (Imperial)

0.75

Bundle Diameter Max (Metric)

19.1

Wall Thickness WT (Imperial)

0.029

Wall Thickness WT (Metric)

0.76

Material

Polyolefin, cross-linked (PO-X)

Material Shortcut

PO-X

Flammability

ASTM D876

Halogen Free

No

UV Resistant (Yes/No)

No

Use Conditions

For Indoor Use Only

Operating Temperature

-67°F to +275°F (-55°C to +135°C)

Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 224
UL Recognized (US)	Yes
Package Quantity (Imperial)	82
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)