

Specification Sheet

Part Number: 558-00380

Continuous Colored Signal Panel labels come with yellow or orange stripes for easy printing of caution and warning labels.

Continuous labels allow for designing and cutting labels to any length.

Various widths are available so that a wide variety of sign sizes can be customized and produced on demand.



Thermal Transfer Adhesive Labels, Banded Color Continuous Roll, 2.0 x 250', UV Stable PET, Orange/White, 250 ft/roll

Article Number	558-00380
Type	HT2OE50250UV
Color	Orange (OG)
Quantity Per	pack
Product Description	Banded colored continuous rolls come with a stripe (band) for easy printing of warning labels. Available in different widths, these labels are designed for use with TagPrint® Pro software and HellermannTyton thermal transfer printers and can be customized, produced on demand and cut to any length.
Short Description	Thermal Transfer Adhesive Labels, Banded Color Continuous Roll, 2.0 x 250', UV Stable PET, Orange/White, 250 ft/roll

Global Part Name	HT2OE50250UV-840/281-OG
Length L (Imperial)	250.0
Length L (Metric)	76.20
Variant	3.2mil, 50lb bleached kraft paper
Width W (Imperial)	2.0
Width W (Metric)	50.8
Thickness T (Metric)	64.0
Width of Liner (Metric)	50.8
Width of Liner (Imperial)	2.0
Material	Type 840/281, Polyester, UV-stabilized, clear polyester laminate (840/281)
Material Shortcut	840/281
Adhesive	Acrylic
Halogen Free	Yes
UV Resistant (Yes/No)	Yes

Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2014 IFC 2012 NEC2011 CSA 66956 UL 969 ANSI Standard Z535.4
UL Recognized (US)	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	76.20
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com