


Specification Sheet

Part Number: TAG27T1-795



Metalized polyester has a matte finish, allowing for the highest resolution and print contrast.

The acrylic-based adhesive bonds to a wide variety of substrates and can withstand high temperatures long term.

Article Number	596-27795
Type	TAG27T1
Color	Silver (SR)
Quantity Per	pack
Product Description	HellermannTyton’s metalized polyester labels include a layer of metallic particles that give the appearance of being made of metal. Applications include asset tracking and product rating plates. The high operating temperature makes them suitable for use on electronic equipment. Great for replacing expensive metal stampings, engravings and even silk screened rating plates, the printed labels offer high quality imaging for text and graphics and can be permanently placed on a wide variety of flat surfaces.
Short Description	Thermal Transfer Adhesive Labels, 1.5 x 0.75", 1 Across, Polyester, Silver, 3000/roll

Global Part Name	TAG27T1-795-SR
Width W (Imperial)	1.5
Width W (Metric)	38.1
Thickness T (Metric)	64.0
Height H (Imperial)	0.75
Height H (Metric)	19.05
Width of Liner (Metric)	55.88
Width of Liner (Imperial)	2.2
Material	Type 795, Polyester (795)
Material Shortcut	795
Adhesive	Acrylic
Halogen Free	Yes
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Operating Temperature	-67°F to +302°F (-55°C to +150°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-Recognized
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes

Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com