

Specification Sheet

Part Number: TAG11L-789



Laser printable white polyester has a smooth surface, allowing for the highest resolution and print contrast.

The acrylic-based adhesive bonds to a wide variety of substrates and can withstand high temperatures long term.

Lasertags are not affected by the high heat required in a laser printer.

Laser Tag Label, 0.65 x 0.20", 480 Per Sheet, Polyester, White, 5000/pkg

Article Number	594-11789
----------------	-----------

Type	TAG11L
------	--------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton white polyester labels are ideal for marking small electrical and electronic components, such as EPROMS', Integrated circuits, as well as the circuit board itself. Printed labels can withstand the soldering process and survive flux removal when the board is washed. HellermannTyton's 789 material is designed for use on flat surfaces and can also be used to identify connectors, buttons and just about anything requiring permanent, durable, high temperature and UV resistant marking.
---------------------	--

Short Description	Laser Tag Label, 0.65 x 0.20", 480 Per Sheet, Polyester, White, 5000/pkg
Global Part Name	TAG11L-789-WH
Width W (Imperial)	0.65
Width W (Metric)	16.5
Thickness T (Metric)	64.0
Height H (Imperial)	0.2
Height H (Metric)	5.08
Material	Type 789, Polyester (789)
Material Shortcut	789
Adhesive	Acrylic
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)

Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3919905060
Labels per Column	48
Labels per Row	10

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com