

Specification Sheet

Part Number: TAG59L-788

LaserTags are sheet fed for easy loading and fast printing.



LaserTags are made with high temperature materials and adhesives so that they will not be affected by the high heat of laser printing.

LaserTags are printable using toner for long term UV exposure.

LaserTags come in a variety of label sizes and types to fit most applications.

Laser Tag Label, 1.5" x 4.0", 14 Per Sheet, PET, White, 3500/pkg

Article Number 594-59788

Type TAG59L

Color White (WH)

Quantity Per pack

Product Description HellermannTyton white polyester labels are ideal for marking small electrical and electronic components, such as EPROMS', Integrated circuits, as well as the circuit board itself. Printed labels can withstand the soldering process and survive flux removal when the board is washed. HellermannTyton's 788 material is designed for use on flat surfaces and can also be used to identify connectors, buttons and just about anything requiring permanent, general purpose marking.

Short Description Laser Tag Label, 1.5" x 4.0", 14 Per Sheet, PET, White, 3500/pkg

Global Part Name

TAG59L-788-WH

Width W (Imperial) 4.0

Width W (Metric) 101.6

Thickness T (Metric) 64.0

Height H (Imperial) 1.500

Height H (Metric) 38.1

Material Type 788, Polyester (788)

Material Shortcut 788

Adhesive Acrylic

Halogen Free No

UV Resistant (Yes/No) No

Use Conditions For Indoor Use Only

Adhesive Operating Temperature -40°F to +199°F (-40°C to +93°C)

Operating Temperature -40°F to +199°F (-40°C to +93°C)

Reach Compliant (Article 33) Yes

ROHS Compliant	Yes
Package Quantity (Imperial)	3500
Package Quantity (Metric)	3500
Customs Number	3919905060
Labels per Column	7
Labels per Row	2

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)