

TECHNICAL DATA SHEET

Part No. ATS10266110
Article No. 102-66110
Type Strap_Black_ATS



The cable tie strap for the ATS Flex is designed for optimized material utilization. This innovative two-piece system consists of a separate strap and closure, eliminating waste and the associated jobsite cleanup.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +203°F (-40°C to +95°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1640 ft
Carton Qty.	4
Customs Number	3926909988

Releasable Closure	No
Length (imperial)	1640.0 ft
Length (metric)	500.0 m
Max. Bundle Diameter (imperial)	3.94 "
Max. Bundle Diameter (metric)	100 mm
Min. Bundle Diameter (imperial)	0 "
Min. Bundle Diameter (metric)	0.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Reel Diameter	387 mm
Reel Diameter (imperial)	15.25 "
Reel Width	88.9 mm
Reel Width (imperial)	3.5 "
Width (imperial)	0.18 "
Width (metric)	4.5 mm

