


TECHNICAL DATA SHEET

Part No. QTTIE0HS
Article No. 105-00001
Type AZ100



HellermannTyton's Quick Tool is an automatic bench mount system suited for high volume cable tie applications. This air powered tool accommodates a reel of 5000 ties and, like HellermannTyton's other automated systems, can be integrated into further automation as well as fully incorporated into conveyor or assembly line applications. Custom colors for Quick Tool ties are also available.

Material	Polyamide 6.6 heat and UV stabilized (PA66HSUV)
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Flammability	UL 94 V-2
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	5000
Carton Qty.	10000
Customs Number	3926909988

Releasable Closure	No
Length (imperial)	3.94 "
Length (metric)	100 mm
Max. Bundle Diameter (imperial)	0.63 "
Max. Bundle Diameter (metric)	16.0 mm
Min. Bundle Diameter (imperial)	0.03 "
Min. Bundle Diameter (metric)	0.7 mm
Min. Tensile Strength (imperial)	18 lbs
Min. Tensile Strength (metric)	80 N
Reel Diameter	450.00 mm
Reel Diameter (imperial)	18 "
Reel Width	132 mm
Reel Width (imperial)	5.2 "
Thickness (metric)	1.1 mm
Width (imperial)	0.1 "
Width (metric)	2.5 mm

RoHS[✓]

