

TECHNICAL DATA SHEET

Part No. MK9PUA
Article No. 110-09112
Type MK9P



The Mark 9 Pneumatic (MK9P) is constructed with heavy duty parts to ensure that it performs optimally in demanding environments. It is ideally designed to apply heavy-duty ties (T50-T250), clamp and button head ties. Like the MK7P, HellermannTyton's MK9P incorporates the next level of ergonomic improvement with its low weight, comfortable grip and easy trigger depression. Very durable, the pneumatic MK9P features adjustable, easy to read tension settings. Lock-out features are available. The MK9P is available with lower air attachment (standard) or can be ordered with an upper air attachment.

Material	Polyamide 6.6, glass fiber reinforced (PA66GF30)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1
Carton Qty.	1
Customs Number	8467195090

Power Supply	Dry or lubricated air
Air Attachment	upper air connection
Air Supply	non lubricated, oiled
Description	Top Air Supply Connection
For Cable Tie Series	T50 - T250 CTT20 - CTT175 EI-TY Button Head
For Cable Tie Width (metric)	4.6 - 13.5 mm
Height (metric)	200 mm
Length (metric)	280 mm
Max. Cable Tie Thickness (imperial)	0.10 "
Max. Cable Tie Thickness (metric)	2.5 mm
Operation	pneumatic
Tension Setting	Adjustable
Width (metric)	55 mm

RoHS ✓