

TECHNICAL DATA SHEET

Part No. 110-88005
Article No. 110-88005
Type EVO9iSP



HellermannTyton's EVO® 9i industrial-grade, mechanical hand tool is ergonomically designed to reduce the risks of repetitive stress injuries to operators while simultaneously increasing productivity. The EVO 9i Tension/Lock/Cut Technology delivers performance, safety and comfort for operators. Calibrated tensioning ensures consistent wire-bundle tension before flush cut-off. Available in a standard grip span (EVO 9i) or short grip span (EVO 9iSP) for smaller hands. The high-tension model (EVO 9iHT) is capable of delivering higher tension forces before locking and cutting the tie. Additional accessories are available.

Material	Metal (MET), Plastic (PL)
Use Conditions	For Indoor Use Only
Color	Blue (BU), Gray (GY)
Pkg. Qty.	1
Carton Qty.	20 EA
Customs Number	8205599000

Description	EVO 9iSP Mechanical Hand Tool, Short Hand Span
For Cable Tie Series	T50, T80, T120, T150, T250, T255, WS, LK2, LK3, LK5, GL, ECO Series
For Cable Tie Width (metric)	4.6 - 13.5 mm
Max. Cable Tie Thickness (imperial)	0.08 "
Max. Cable Tie Thickness (metric)	2.0 mm
Operation	manual
Tension force (N)	53 - 307 N
Tension Range lbs.	12 - 69 lbs
Tension Setting	Adjustable

RoHS ✓