

TECHNICAL DATA SHEET

Part No. T250I0X2
Article No. 111-00507
Type T250I



These cable ties offer a high minimum tensile strength and have a buckle feature which allows the end of the cable tie to be tucked away if necessary. The buckle also snaps into HellermannTyton lashing tie mounts (LTM.) T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
Plenum Rating	AH-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	25
Carton Qty.	500
Customs Number	3926909988

Cable Tie Head Length (imperial)	0.88 "
Cable Tie Head Length (metric)	22.4 mm
Cable Tie Head Width (imperial)	0.8 "
Cable Tie Head Width (metric)	20.0 mm
Height (imperial)	0.37 "
Height (metric)	9.5 mm
Length (imperial)	28.7 "
Length (metric)	730.0 mm
Max. Bundle Diameter (imperial)	7.99 "
Max. Bundle Diameter (metric)	203.0 mm
Min. Tensile Strength (imperial)	250 lbs
Min. Tensile Strength (metric)	1115 N
Serration Side	Inside Serrated
Thickness (imperial)	0.09 "
Thickness (metric)	2.2 mm
Width (imperial)	0.49 "
Width (metric)	12.4 mm

