

TECHNICAL DATA SHEET

Part No. AT510266210
Article No. 102-66210
Type Closures_Black_ATS



The cable tie closure for the ATS Flex is designed for optimized material utilization. This innovative two-piece system consists of a separate strap and closure, eliminating waste and the associated jobsite cleanup.

Material	Polyamide 6.6 heat and UV stabilized (PA66HSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	5000
Carton Qty.	4
Customs Number	3926909988

Releasable Closure	No
Length (imperial)	0.35 "
Length (metric)	9.0 mm
Max. Bundle Diameter (imperial)	3.94 "
Max. Bundle Diameter (metric)	100 mm
Min. Bundle Diameter (imperial)	0 "
Min. Bundle Diameter (metric)	0.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Reel Diameter	387 mm
Reel Diameter (imperial)	15.25 "
Reel Width	88.9 mm
Reel Width (imperial)	3.5 "
Width (imperial)	0.31 "
Width (metric)	8.0 mm

