

TECHNICAL DATA SHEET

Part No. MK7P
Article No. 110-07101
Type MK7P



The Mark 7 Pneumatic (MK7P) industrial-grade cable tie application tool is built to perform in demanding production and manufacturing environments. Heavy duty precision parts ensure repeatability in the tensioning process. The MK7P is ergonomically designed for operator comfort, reducing hand, arm and wrist fatigue. It consistently maintains the correct tension and provides a flush, safe cut-off with no sharp edges.

Material	Polyamide 6.6, glass fiber reinforced (PA66GF30)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1
Carton Qty.	1
Customs Number	8467195090

Power Supply	Dry or lubricated air
Air Attachment	lower air connection
Air Supply	non lubricated, oiled
Description	Mark 7 Pneumatic Tool
For Cable Tie Series	T18 - T50, CTT20 - CTT60
For Cable Tie Width (metric)	2.5 - 4.8 mm
Height (metric)	170 mm
Length (metric)	220 mm
Max. Cable Tie Thickness (imperial)	0.06 "
Max. Cable Tie Thickness (metric)	1.5 mm
Operation	pneumatic
Tension force (N)	60-170 N
Tension Setting	Adjustable
Width (metric)	40 mm

