

TECHNICAL DATA SHEET

Part No. 111-00884
Article No. 111-00884
Type T40S



Part of our sustainable line of products, the EarthSource product family features solutions made from abundant plant fibers and other natural elements. This inside-serrated cable tie is manufactured from Polyamide 11, which is 100 percent bio-based from sustainable castor oil plants. The material provides excellent UV, chemical and moisture resistance to allow for a longer lifespan in outdoor use. It is recommended for applications exposed to metal oxides. The head design guarantees high tensile strength, as well as a low insertion force. Tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 11 (PA11)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor Use Only
Color	Translucent (TT)
Pkg. Qty.	100
Carton Qty.	10000
Customs Number	3926909988

Length (imperial)	6.02 "
Length (metric)	153.0 mm
Max. Bundle Diameter (imperial)	1.46 "
Max. Bundle Diameter (metric)	37.0 mm
Min. Tensile Strength (imperial)	30 lbs
Min. Tensile Strength (metric)	130 N
Serration Side	Inside Serrated
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.14 "
Width (metric)	3.5 mm

