

TECHNICAL DATA SHEET

Part No. 111-00925
Article No. 111-00925
Type T250M



Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. The bent tail allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 6.6 UV-stabilized (PA66UV)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	25
Carton Qty.	500
Customs Number	3926909988

Length (imperial)	22.3 "
Length (metric)	565.3 mm
Max. Bundle Diameter (imperial)	5.91 "
Max. Bundle Diameter (metric)	150.0 mm
Min. Tensile Strength (imperial)	250 lbs
Min. Tensile Strength (metric)	1115 N
Serration Side	Inside Serrated
Thickness (imperial)	0.07 "
Thickness (metric)	1.9 mm
Width (imperial)	0.49 "
Width (metric)	12.4 mm

