

TECHNICAL DATA SHEET

Part No. 111-01563
Article No. 111-01563
Type T50XL



This inside serrated cable tie is manufactured from PA12, which provides excellent UV, chemical and moisture resistance to allow for a longer lifespan in outdoor use. PA12 material absorbs slightly less moisture than PA11, yet is equally resistant to metal oxides. HellermannTyton T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail allows quick and simple installation by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Material	Polyamide 12 (PA12)
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Length (imperial)	18.0 "
Length (metric)	467.6 mm
Max. Bundle Diameter (imperial)	5.28 "
Max. Bundle Diameter (metric)	134.0 mm
Min. Tensile Strength (imperial)	45 lbs
Min. Tensile Strength (metric)	200 N
Serration Side	Inside Serrated
Thickness (imperial)	0.06 "
Thickness (metric)	1.4 mm
Width (imperial)	0.19 "
Width (metric)	4.8 mm

