

TECHNICAL DATA SHEET

Part No. 111-01671
Article No. 111-01671
Type TAS120M



Aerial Support Ties feature a built-in spacer to separate cables from the support wire and prevent abrasion. A one-piece design, combining the tie and spacer into one part, reduces installation time and inventory costs. The outside serrations along the strap prevent damage to cables. Formulated from a special nylon blend, these ties are specifically suited for long-term outdoor use. The bent tail allows for quick and simple installation by hand.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	500
Customs Number	3926909988

Height (imperial)	0.76 "
Height (metric)	19.0 mm
Length (imperial)	12.4 "
Length (metric)	270.0 mm
Max. Bundle Diameter (imperial)	2.76 "
Max. Bundle Diameter (metric)	70.0 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Thickness (imperial)	0.062 "
Thickness (metric)	1.58 mm
Width (imperial)	0.5 "
Width (metric)	12.7 mm

HF ✓

RoHS ✓